

Floway2® roller track and basic support

RAG- FLOW2

Principal of operation




- The Floway-2® roller track allows storage systems to be created for plastic boxes or cardboard cartons

Support



- For easy installation of roller tracks
- Suitable for use in gravity feed conveyors
- Material:
Electro-galvanised steel

Assembly

- Slide the roller track into the end support
- Position the complete assembly on the supporting structure
- Track can be locked in place using a screw (tapped hole to be drilled on site)



Basic support



Support with stop



Floway2® roller track and basic support

For transporting and storage

RAG-FLOW2


- High density polyethylene roller
- Chromed steel guide (no deformation under load)
- Rollers rotate on steel axles
- Colour: Black

Special Features


- The possibility of being able to stagger the position of the rails increases the performance of the system



Roller track




Basic support



RAG-FLOW2-A

Support with stop



RAG-FLOW2-B

DISCOUNTS Roller track DISCOUNTS Basic support

Qté	1+	5+	10+	Qté	1+	50+	100+
Disc. Prix	-5%	On request	On request	Disc. Prix	-5%	On request	On request

Roller track


Part number	P1	P2	Length L	N° of with roller rollers	Max load per roller (kg)	Stock*	Price each
							1 à 4
RAG-FLOW2-1000	35	41	1000 ±1	980	34	10	✓ 24,51 €
RAG-FLOW2-2000	35	33	2046 ±1	2016	70	10	✓ 40,33 €

Basic support

Part number	Description	Thickness	Weight (g)	Stock*	Price each
					1 à 49
RAG-FLOW2-A	Basic support	2	124	✓	8,16 €
RAG-FLOW2-B	Support with stop	2	141	-	8,16 €

*Subject to available stocks - Dimensions in mm

Our other products




RPPM
RPP type belt per metre, RPP8 Steel cored polyurethane



FF30
Offset spur gear reducer, from 21.50 to 83 Nm



PTA150
Articulated levelling foot, pressed base Ø150, Ø 150



NK80
Drylin®N miniature guiding system, Width 80mm



ADSR
Backlash free coupling Gerwah®, from 12.5 to 525Nm



PRF_BP
Doorstop for aluminium profile, Swing door stop



HRV
V-rail guidance Simple Select® system, Rail with carriage



CTss
Universal joint, telescopic, Inox, Light duty




RAGFLOWsupport
Floway2® Roller track accessory, Roller



PSG25
Spur gear - precision range, Stainless steel



LC
Friction clutch, 190 to 1800 Nm



CRM
Moulded nylon rack, Nylon

Complementary products



RAGFLOW
Floway2® roller track, Roller track



RAGb
Cylindrical brush track, For gentle conveying and handling