


Shaft support for aluminium profile Stock

PRFPSA **MiniTec** Z12 For attaching a guidance shaft to a profile

- Support profile for linear guide shafts

- Materials:

- Profile: anodised aluminium E6/V1
- Steel shaft: Cf53 hardened (62 +/-2 HRC) Stainless steel shaft: hardened stainless steel X90CrMoV18 (57 +/-2 HRC)
- Shaft end stop: grey power coated aluminium (Fixing kit supplied)




Assembly


- Insert the shaft support profile into the profile slot
- Secure with M5x10 grub screws
- Insert the shaft into the support profile with the aid of a plastic mallet if necessary

Accessories

- Roller PRF-GAL-12
- Shaft end stop PRF-12-AA



PRF-12-PSA



PRF-12-AA

DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

DISCOUNTS Shafts Z

Qty	1+	6+	20+	40+	60+
Disc.	List	-20%	-25%	-30%	On request

Part number	For profile	Material	Length	Weight (kg/m)	Stock*	Price each
Shaft support profile						
PRF-12-PSA	all types	-	3000	0,36	✓	24,59 €
Linear guidance shaft						
Z-12-3000A		steel	3000	0,89	-	49,61 €
Z-12-3000B		stainless steel	3000	0,89	-	159,73 €
Shaft end stop						
PRF-12-AA		-	-	0,03	✓	6,66 €

*Depending on availability - Dimensions in mm

Our other products



MSP23

Masterplate® glueable insert Ø23, Cylindrical Ø23 with threaded s...



PHTss

Pull handle, Up to 250 °C



BEK

Bearing housing for miniature ballscrew, Bearing housing



BC3

Panamech, Multi-Beam stainless steel, Stainless steel - with clampin...



DB

Steel bevel gear, 2:1



NT91

Spur gear coaxial gearbox, from 10 to 35 Nm - Inline



RAS

90°ball and socket joints DIN71802, Steel



ABL100005

Antistatic brush, Standard



G2

Steel spur gear, Steel 20NCD2



PRF-SMA

Closing system for aluminium profile,



CHT

Asynchronous AC Motor, 0.18 to 0.55kW



PW_PWG15


Worm - precision range, Stainless steel

Complementary products



PRF_GAL

Roller for aluminium profile, Hollow roller ø12



PRF_PSA

Shaft support for aluminium profile, Shaft stop