

Stainless steel articulated foot Ø100

PRS100

Maximum load 55.000N


- Levelling foot with solid base
- Non slip base
- Materials:
 - Base: stainless steel AISI 304
 - Threaded rod: stainless steel AISI 304 (nut not supplied)
 - Sole: NBR rubber (Shore hardness 70)

stainless steel



Advantages

- Articulated rod allows auto-alignment with the ground
- Sole material ensure




DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØM	A	B	ØD	A/F	G	H	H1	Max. load (N)	Price each
										1 to 5
PRS100-16-75	M16	43	75	100	20	20	118	121	35000	103,90 €
PRS100-16-100	M16	43	100	100	20	20	143	146	35000	107,69 €
PRS100-16-125	M16	43	125	100	20	20	168	171	35000	110,61 €
PRS100-16-150	M16	43	150	100	20	20	193	196	35000	113,89 €
PRS100-16-175	M16	43	175	100	20	20	218	221	35000	116,02 €
PRS100-16-200	M16	43	200	100	20	20	243	246	35000	122,25 €
PRS100-20-75	M20	43	75	100	20	20	118	121	45000	103,90 €
PRS100-20-100	M20	43	100	100	20	20	143	146	45000	100,55 €
PRS100-20-125	M20	43	125	100	20	20	168	171	45000	110,61 €
PRS100-20-150	M20	43	150	100	20	20	193	196	45000	113,89 €
PRS100-20-175	M20	43	175	100	20	20	218	221	45000	116,02 €
PRS100-20-200	M20	43	200	100	20	20	243	246	45000	122,25 €
PRS100-20-225	M20	43	225	100	20	20	268	271	45000	125,83 €
PRS100-20-250	M20	43	250	100	20	20	293	296	45000	130,27 €
PRS100-24-75	M24	44	75	100	20	20	119	122	55000	103,90 €
PRS100-24-100	M24	44	100	100	20	20	144	147	55000	107,69 €
PRS100-24-125	M24	44	125	100	20	20	169	172	55000	110,61 €
PRS100-24-150	M24	44	150	100	20	20	199	202	55000	113,89 €
PRS100-24-175	M24	44	175	100	20	20	219	222	55000	116,02 €
PRS100-24-200	M24	44	200	100	20	20	244	247	55000	122,25 €
PRS100-24-225	M24	44	225	100	20	20	269	272	55000	125,83 €
PRS100-24-250	M24	44	250	100	20	20	294	297	55000	130,27 €

Dimensions in mm

Our other products



KS

Keysteel, Stainless steel - Keystock



PR820

Idler sprocket for slat top chain, Rangs 820 and 815



PW_PWG3

Worm - precision range, Stainless steel



B52

Panamech, Multi-Beam, Aluminium - with set screw



PSG15

Spur gear - precision range, Case hardened steel 20NCD2



T10courroie

T type timing belt, T10 Steel cored polyurethane



BLH30

Right angled gearbox, from 1.32 to 4.40 Nm



H1

Crossed helical gear crossed axis at 90°, Steel 20NCD2



PW_PWG2

Worm - precision range, Steel



CMM

Male rod ends DIN ISO12240-4, Steel /



M2

Worm and wheel set, Unhardened steel



PW_PWG1

Wheel - precision range, Bronze

Complementary products