

High Temperature Castors



RHTPLSS

Load up to 200kg

- **High temperature industrial castor**
- Swivel system on 2 crowns of balls
- Double-locking swivel castor:
use the foot pedal to lock and unlock.
- Slide bearings
- Materials:
304 stainless steel sheet
Polyamide wheel (see RHT)
- Working temp.: -30°C to +280°C



Fixed



Swivel

Advantages

- Large storage capacity
- Resists high temperatures



Double locking swivel



ØD



B



H



L



M



T



ØK

DISCOUNTS

Qty	1+	5+	15+
Disc. Price	-5%	On request	

Part number	ØD	B	H	L	M	ØT	Circle interference ØK	Load maximum (kg)	Price per unit 1 to 4
Fixed									
RHT80/PL/F/SS	80	35	105	115x83	80x60	11x9		125	32,70 €
RHT100/PL/F/SS	100	35	126	115x83	80x60	11x9		150	33,33 €
RHT125/PL/F/SS	125	40	153	115x83	80x60	11x9		200	76,05 €
Swivel									
RHT80/PL/P/SS	80	35	105	115x83	80x60	11x9	173	125	40,77 €
RHT100/PL/P/SS	100	35	126	115x83	80x60	11x9	193	150	41,93 €
RHT125/PL/P/SS	125	40	153	115x83	80x60	11x9	221	200	85,28 €
Double locking swivel									
RHT80/PL/PDB/SS	80	35	105	115x83	80x60	11x9	293	125	49,34 €
RHT100/PL/PDB/SS	100	35	126	115x83	80x60	11x9	293	150	50,50 €
RHT125/PL/PDB/SS	125	40	153	115x83	80x60	11x9	293	200	93,85 €

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



CHAPAMss

Weld-on hinge with flat end, Stainless steel or Aluminium



LFM2

Steel leadscrew, Medium carbon steel - 2 threads



BH01

Single housed bearing, Bearing fitted with adhesive



RBGpl

Swivel castor with plate, Steel - grey rubber



RPB

Ballscrew bearing unit, Support



AC156-157

Strike for toggle latch, 25.5mm



WSS

Symmetrical S shaped hook, Steel



AT10courroie

AT type timing belt, AT10 Steel cored polyurethane



GMK17_BR

Clamp for guiding profile, Rounded only



PSG35

Spur gear - precision range, Stainless steel



KK

Rounded end feather key, Steel



BTC

End cap for square tube, Standard

Complementary products



RHTtcss

High Temperature Castor, up to 200kg



RHTtcss

High Temperature Castor, up to 200kg



RHT

High Temperature wheel, up to 200kg



RHTplss

High Temperature Castor, up to 200kg