

# Locking castor with mounting plate

For loads up to 1000kg

RIM



- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C



Adjusting nut

## Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate square
- Wheel: Black polyamide Shore D 70



## DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	L	M	ØT	Swivel interference		Load (kg)	Price each 1 to 5
								ØK			
RIM42-60/PLE	42	20	71	81	55x55	42x42	6,5	84		60	46,66 €
RIM50-280/PLE	50	25	82	92	73x73	58x58	7	101		280	74,11 €
RIM63-550/PLE	63	28	103	118	90x90	70x70	9	125		550	100,71 €
RIM75-800/PLE	75	30	120	132	95x95	70x70	11	142		800	111,33 €
RIM75-1000/PLE	75	30	120	132	95x95	70x70	11	142		1000	132,76 €

Dimensions in mm

## Our other products



T25-6ECO

T type timing pulley,  
Economy range - T2.5  
aluminium



BLHB20

Right angled gearbox,  
bored shafts, up to  
1.77 Nm



PW\_PWG1

Wheel - precision  
range, Bronze



VMS

Stainless steel knurled  
thumb screw, Knurled



HTD8M\_50

HTD Heavy duty  
timing pulley, HTD8  
Cast



PAMF100EB

Articulated foot with  
sheet metal base  
Ø100, Articulated foot




DPAR\_DKON

Conical elasto buffer,  
Steel



PRF\_SDD

Support for Ø12mm  
Prox detector, Ø12



B

Steel bevel gear, 1:1



DBC

Panamech, Multi-  
Beam, Aluminium -



HTD14M\_55

HTD Heavy duty  
timing pulley, HTD14



TB\_ECO

Eco. range steel bevel  
gear, 3:1

## Complementary products



RIMtce

Locking castor, with  
central hole



PDR-RD

Mounting feet with  
integrated castors,  
Offset castor