

# Locking castor with central hole



## RIM

## For loads up to 1000kg



- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C

### Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate has a threaded central hole, threaded rod and nut supplied.
- Wheel: Black polyamide Shore D 70



Adjusting  
nut



### DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	ØT	Swivel interference ØK	Load (kg)	Price each 1 to 5
RIM42-60/TCE	42	20	71	81	M8	84	60	46,66 €
RIM50-280/TCE	50	25	82	92	M12	101	280	74,11 €
RIM63-550/TCE	63	28	103	118	M12	125	550	100,71 €
RIM75-800/TCE	75	30	120	132	M16	142	800	111,33 €
RIM75-1000/TCE	75	30	120	132	M16	142	1000	132,76 €

Dimensions in mm


## Our other products



RIMtce  
Locking castor, with central hole



PRF-SCREEN-1  
Screen support, Basic support



PRF\_TOOL  
Assembly key for aluminium profile, Assembly key



BZY  
Cylindrical elasto mount, Steel



T5-10ECO  
T type timing pulley, Economy range - T5 aluminium



PT821  
Drive sprocket for slat top chain, Ranges 821 and 805



BCFH  
Mushroom headed button Hygienic Usit®, With male thread and high head



J65  
Spur gear coaxial gearbox, from 0.80 to 2.95 Nm - Inline



CHAEss  
Decorative hinge, Stainless steel



HG6-ECO  
Eco range Spur gear, Steel C45



PTA40  
Articulated foot with solid base foot Ø 40,



UTKswr  
Utilitak® V rail, V rail

## Complementary products



RIMple  
Locking castor, with mounting plate



PDR-RD  
Mounting feet with integrated castors, Offset castor