


- For driving CAP820 and CAP815 plate chains
- With bore and keyway
- Materials:
 - Reinforced polyamide
 - Stainless steel screws
- Operating temp.: -10°C to +120°C
- For dimensions and bore tolerances, please refer to technical pages


Advantage

- Two part design facilitates easy assembly

Easy assembly



Two part design



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PT820-21-25	21	129	129,26	25	0,4	30,67 €
PT820-21-30	21	129	129,26	30	0,4	30,67 €
PT820-21-35	21	129	129,26	35	0,4	30,67 €
PT820-21-40	21	129	129,26	40	0,4	30,67 €
PT820-21-45	21	129	129,26	45	0,4	30,67 €
PT820-23-25	23	141	141,22	25	0,5	32,38 €
PT820-23-30	23	141	141,22	30	0,5	32,38 €
PT820-23-35	23	141	141,22	35	0,5	32,38 €
PT820-23-40	23	141	141,22	40	0,5	32,38 €
PT820-23-45	23	141	141,22	45	0,5	32,38 €
PT820-25-25	25	153	153,20	25	0,5	32,71 €
PT820-25-30	25	153	153,20	30	0,5	32,71 €
PT820-25-35	25	153	153,20	35	0,5	32,71 €
PT820-25-40	25	153	153,20	40	0,5	32,71 €
PT820-25-45	25	153	153,20	45	0,5	32,71 €

Dimensions in mm

Our other products



SHW
Plain washer, Steel




SVG
Adjustable latch
clamp with strike
plate, Stroke from
118mm to 130,5mm



BABss
303 Stainless steel
ball pin, 303 Stainless
steel




GP
Spring loaded toggle
latch, With padlock-
holder



MF
Shock Absorber
-universal flange,
Universal fixing



T10_21N1F
T type timing pulley,
Economy range - T10
moulded plastic
(nylon)



BCM_HPBT
Modular cylindrical
brush, PBT polyester
bristles



PSG05HC
Skive hobbled spur
gears - precision
range, Case hardened
steel 20NCD2



ARTE
Flexible bush, For
multi-directional loads



D-PAR_SS
Stainless steel elasto
mount, stainless steel



LRR-53
Spring loaded latch,
Spring return latch -
steel



AT5M_AT10M
AT type timing belt
per metre, AT10 Steel
cored polyurethane

Complementary products



CAP820
Slim slat top chain
acetal, Narrow
straight range 820



CAP815
Slim slat top chain
stainless steel,
Narrow range 815



DBL820
Idler for slat top
chain, Ranges 820
and 815



BAP25
Plastic clamping
collar, Ø25 - Ø40