



Stainless steel swivelling foot

Max load 25,000N




- "Teknohygienic" swivelling foot
- Materials:
 - Base: stainless steel 304
 - Stem: stainless steel 304
 - Sole: NBR rubber Shore hardness 90°

Advantages

- The 3-A standard designates products that are designed for the dairy, food and pharmaceutical industries where strict hygiene rules apply.
- Smooth finished foot with a wiper seal between the stem and the nut and around the swivel to prevent accumulation of dirt or retention of water
- Suitable for cleaning with water or chemicals
- USDA approved

For the food industry
stainless steel

Avoids water retention



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	Adjustable range E	A	B	ØD	SW	ØD1	ØD2	G	CH	H1	H2	H3	Static load (N)	Price each 1 to 5
PTK80-16-140/SS	M16	45	53	140	80	13	24	60	25	20	193	114	159	20000	95,45 €
PTK80-16-190/SS	M16	70	53	190	80	13	24	85	25	20	243	139	209	20000	114,59 €
PTK80-20-140/SS	M20	45	53	140	80	17	30	60	25	26	193	114	159	20000	100,23 €
PTK80-20-142/SS	M20	55	53	142	80	17	30	70	25	26	195	123	178	20000	103,55 €
PTK80-20-190/SS	M20	70	53	190	80	17	30	85	25	26	243	139	209	20000	115,62 €
PTK80-24-140/SS	M24	45	53	140	80	20	35	60	25	30	193	114	159	20000	108,97 €
PTK80-24-190/SS	M24	70	53	190	80	20	35	85	25	30	243	139	209	20000	123,53 €
PTK100-16-140/SS	M16	45	56	140	100	13	24	60	28	20	196	117	162	25000	100,02 €
PTK100-16-190/SS	M16	70	56	190	100	13	24	85	28	20	246	142	212	25000	119,17 €
PTK100-20-140/SS	M20	45	56	140	100	17	30	60	28	26	196	117	162	25000	104,82 €
PTK100-20-190/SS	M20	70	56	190	100	17	30	85	28	26	246	142	212	25000	120,18 €
PTK100-24-140/SS	M24	45	56	140	100	20	35	60	28	30	196	117	162	25000	113,54 €
PTK100-24-190/SS	M24	70	56	190	100	20	35	85	28	30	246	142	212	25000	128,12 €
PTK100-30-135/SS	M30	40	56	135	100	26	42	60	28	36	191	117	157	25000	124,77 €
PTK100-30-185/SS	M30	65	56	185	100	26	42	85	28	36	241	142	207	25000	136,40 €

Dimensions in mm

- "Teknohygienic" swivelling foot

- Materials:

Base: stainless steel 304

Stem: stainless steel 304

Blind nut: stainless steel 304

- Sole: NBR rubber Shore hardness 90°

Advantages

- The 3-A standard designates products that are designed for the dairy, food and pharmaceutical industries where strict hygiene rules apply.

- Smooth finished foot with a wiper seal between the stem and the nut and around the swivel to prevent accumulation of dirt or retention of water


- Suitable for cleaning with water or chemicals

- USDA approved

Info.

- Do not forget to order the **PTKF-M12/SS**

3-A approved blind nut



For the food industry

stainless steel



Blind M12 nut

DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	Adjustable range	E	A	B	ØD	SW	ØD1	D2	CH	H2	H3	H1	I	Static load (N)	Price each 1 to 5
PTKF80-16-140/SS	M16	45	53	140	80	13	24	60	20	114	159	193	54	20000	115,89 €
PTKF80-16-190/SS	M16	70	53	190	80	13	24	85	20	139	209	243	54	20000	119,17 €
PTKF80-20-140/SS	M20	45	53	140	80	17	30	60	26	114	159	193	54	20000	104,82 €
PTKF80-20-142/SS	M20	55	53	142	80	17	30	70	26	123	178	195	54	20000	108,15 €
PTKF80-20-190/SS	M20	70	53	190	80	17	30	85	26	139	209	243	54	20000	120,18 €
PTKF80-24-140/SS	M24	45	53	140	80	20	35	60	30	114	159	193	54	20000	108,85 €
PTKF80-24-190/SS	M24	70	53	190	80	20	35	85	30	139	209	243	54	20000	128,12 €
PTKF100-16-140/SS	M16	45	56	140	100	13	24	60	20	117	162	196	69	25000	105,83 €
PTKF100-16-190/SS	M16	70	56	190	100	13	24	85	20	142	212	246	69	25000	124,99 €
PTKF100-20-140/SS	M20	45	56	140	100	17	30	60	26	117	162	196	69	25000	110,64 €
PTKF100-20-190/SS	M20	70	56	190	100	17	30	85	26	142	212	246	69	25000	126,02 €
PTKF100-24-140/SS	M24	45	56	140	100	20	35	60	30	117	162	196	69	25000	119,38 €
PTKF100-24-190/SS	M24	70	56	190	100	20	35	85	30	142	212	246	69	25000	133,93 €
PTKF100-30-135/SS	M30	40	56	135	100	26	42	60	36	117	157	191	69	25000	130,59 €
PTKF100-30-185/SS	M30	65	56	185	100	26	42	85	36	142	207	241	69	25000	142,24 €

Blind M12 nut

PTKF-M12/SS	M12														17	14,93 €
-------------	-----	--	--	--	--	--	--	--	--	--	--	--	--	--	----	---------

Dimensions in mm