

PW Worm and wheel set

PSW Worm available in pre-treated or **stainless steel**

Module 1,0



- Quality grade 7e25 DIN 3974
- Pressure angle: 20°
- Material:
 - Pre-treated steel 35NCD6, 28HRC
 - Stainless steel 303
- Tooth thickness conforms to DIN 3967



Info.

- Torque figures are for 100 rpm and are given as a guide only.

Quality grade 7e25



DISCOUNTS

Qty	1+	6+	19+	50+
Disc.	List	-5%	-10%	On request

Part number		No of starts	Price each 1 to 5	
Steel	Stainless steel		Steel	Stainless steel
PW1.0-1	PW1.0-1S	1	58,91 €	70,70 €
PW1.0-2	PW1.0-2S	2	58,91 €	70,70 €
PW1.0-3	PW1.0-3S	3	58,91 €	70,70 €
PW1.0-4	PW1.0-4S	4	58,91 €	70,70 €
Shaft worm				
PSW1.0-1	PSW1.0-1S	1	95,29 €	114,37 €
PSW1.0-2	PSW1.0-2S	2	95,29 €	114,37 €
PSW1.0-3	PSW1.0-3S	3	95,29 €	114,37 €
PSW1.0-4	PSW1.0-4S	4	95,29 €	114,37 €

Dimensions in mm

Worm and wheel set

PWG

Bronze wheel

**Module
1,0**


- Quality grade 7e25 DIN 3974
- Pressure angle: 20°
- Material: Bronze CA104 (CuAl10Ni5Fe4)
- Tooth thickness conforms to DIN 3967

Options

- Alternative bores (H7)
- Keyway conforming to DIN6885 (J59)
- Tapped hole
- Hole for dowel pin

Info.

- Torque figures are for 100 rpm and are given as a guide only.
- To order, add the number of starts to the part number:
e.g. worm PW1,0-4, wheel PWG1,0-15-4



DISCOUNTS

Qty	1+	6+	19+	50+
Disc.	List	-5%	-10%	On request

Part number	No of teeth	a	ØD	ØDa	ØDe	Bore ØA	ØM	Theoretical backlash (mm)		Torque (Nm)	Price each 1 to 5
								Max.	Min.		
PWG1.0-15-1	15	15,00	15	17	18	5	12	0,112	-0,042	2,05	63,07 €
PWG1.0-16-1	16	15,50	16	18	19	5	12	0,112	-0,042	2,31	64,59 €
PWG1.0-17-1	17	16,00	17	19	20	5	12	0,112	-0,042	2,57	65,01 €
PWG1.0-18-1	18	16,50	18	20	21	5	12	0,112	-0,042	2,85	65,76 €
PWG1.0-19-1	19	17,00	19	21	22	5	12	0,112	-0,042	3,14	65,98 €
PWG1.0-20-1	20	17,50	20	22	23	5	12	0,112	-0,042	3,45	66,37 €
PWG1.0-21-1	21	18,00	21	23	24	5	12	0,112	-0,042	3,76	66,74 €
PWG1.0-22-1	22	18,50	22	24	25	5	12	0,114	-0,040	4,09	67,43 €
PWG1.0-23-1	23	19,00	23	25	26	5	12	0,114	-0,040	4,43	68,06 €
PWG1.0-24-1	24	19,50	24	26	27	6	20	0,114	-0,040	4,79	69,98 €
PWG1.0-25-1	25	20,00	25	27	28	6	20	0,114	-0,040	5,15	72,95 €
PWG1.0-26-1	26	20,50	26	28	29	6	20	0,114	-0,040	5,53	73,84 €
PWG1.0-27-1	27	21,00	27	29	30	6	20	0,114	-0,040	5,92	75,24 €
PWG1.0-28-1	28	21,50	28	30	31	6	20	0,114	-0,040	6,32	75,75 €
PWG1.0-29-1	29	22,00	29	31	32	8	25	0,114	-0,040	6,73	77,02 €
PWG1.0-30-1	30	22,50	30	32	33	8	25	0,114	-0,040	7,15	78,14 €
PWG1.0-35-1	35	25,00	35	37	38	8	25	0,114	-0,040	9,44	94,45 €
PWG1.0-40-1	40	27,50	40	42	43	10	35	0,114	-0,040	12,00	110,91 €
PWG1.0-45-1	45	30,00	45	47	48	10	35	0,114	-0,040	14,84	128,64 €
PWG1.0-48-1	48	31,50	48	50	51	10	35	0,116	-0,038	16,67	137,63 €
PWG1.0-50-1	50	32,50	50	52	53	10	35	0,116	-0,038	17,94	148,07 €
PWG1.0-52-1	52	33,50	52	54	55	10	35	0,136	-0,048	19,25	150,47 €
PWG1.0-55-1	55	35,00	55	57	58	10	35	0,136	-0,048	21,29	155,66 €
PWG1.0-60-1	60	37,50	60	62	63	10	40	0,136	-0,048	24,90	163,08 €
PWG1.0-65-1	65	40,00	65	67	68	10	40	0,136	-0,048	28,76	176,43 €
PWG1.0-70-1	70	42,50	70	72	73	10	40	0,136	-0,048	32,87	190,44 €
PWG1.0-75-1	75	45,00	75	77	78	10	40	0,136	-0,048	37,21	199,69 €
PWG1.0-80-1	80	47,50	80	82	83	10	50	0,136	-0,048	41,80	242,19 €

Wheels available with 15 to 80 teeth

Dimensions in mm

Our other products



ACLRP

Wheel for aluminium profile, Integrated bearing



BPHRF

Ball transfer unit housed spring loaded, High



LVT

Miniature motorised actuator 2A, 2 amper



GCA

Linch pin, Linch



CTss

Universal joint, telescopic, Inox, Light duty



TBEASE

Base plate for economic mini-table, Allows X-Y cross tables



BSM

Spring plunger with internal hexagonal socket, steel body, plastic pin



CHAE4060PA

Decorative asymmetric screwed hinge, Polyamide




LC

Friction clutch, 190 to 1800 Nm



LVT

Miniature motorised actuator 1A, 1 amper



RPP

Connecting plate for RPP type timing belts,



BPM

Slotted spring plunger with ball tip, Steel

Complementary products



PW_PWG1

Worm - precision range, Stainless steel



PW_PWG1

Wheel - precision range, Bronze