


## SZZ

## With protective shields

- Radial contact ball bearings
- Single row of balls
- With 2 protective shields (ZZ joints)
- Tolerance: P6/ABEC3
- Material: stainless steel AISI 440C
- Static and dynamic loads : these bearings can handle approx 70% of the same loads that an equivalent steel bearing will accept
- Max. working temperature: +80°C



stainless steel



### DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØA	ØD	E	Dynamic load (N)	Static load (N)	Stock*	Price each 1 to 5
S682ZZ	2	5	2,3	137,29	39,23	✓	23,04 €
S683ZZ	3	7	3,0	254,97	78,45	✓	17,23 €
S684ZZ	4	9	4,0	509,95	176,52	✓	17,23 €
S685ZZ	5	11	5,0	598,21	225,55	✓	16,30 €
S686ZZ	6	13	5,0	853,18	343,23	✓	16,30 €
S687ZZ	7	14	5,0	961,05	402,07	✓	17,30 €
S688ZZ	8	16	5,0	1029,70	460,91	✓	19,88 €
S608ZZ	8	22	7,0	2726,25	1068,92	✓	35,35 €
S689ZZ	9	17	6,0	1098,34	529,56	-	21,17 €
S6800ZZ	10	19	5,0	1441,58	657,05	✓	38,63 €
S6801ZZ	12	21	5,0	1569,06	853,18	✓	52,95 €
S6802ZZ	15	24	5,0	2029,98	1225,83	✓	67,11 €
S6803ZZ	17	26	5,0	1824,04	1196,41	-	73,48 €
S6804ZZ	20	32	7,0	3314,65	2029,98	✓	87,13 €

\*Depending on availability - Dimensions in mm

## Our other products



Q6  
Deep groove ball bearing, Steel



PW\_PWG15  
Worm - precision range, Stainless steel




RFVcap  
Stainless steel protective cover, Open protective cover



RBG  
Wheel, Grey rubber - Polypropylene rim



CLA  
Clamping lever Hygienic Usit® - female, Stainless steel



RPPM  
RPP type belt per metre, RPP14 Steel cored polyurethane



Q7  
Angular contact ball bearing, Steel



RVM14  
Manual worm and wheel gearbox, Worm/wheel



PRES4HR  
Manual workbench press, Force up to 600kg



ACL  
Joints for aluminium profile, Variable angle hinge



CHT56  
Asynchronous AC motor, 0.09kW



CHV  
Mechanical speed variator, from 0,18 to 1,5kW

## Complementary products



SF\_ZZ  
Deep groove ball bearing, Stainless steel



S\_2RS  
Deep groove ball bearing, Stainless steel



FUSS  
Bearing locknut, Self locking locknut - stainless steel lock washer