

- Closed housing
- SA: Housing only
- SAKH** : Housing and light KH bearing with seal
- Material: anodised aluminium

Accessories



- Hardened ground shafts Z-A, Z-B
- End support for shafts FGWA, SFWR



SA: housing only



SAKH: housing + KH bearing



DISCOUNTS

Qty	1+	5+	10+	25+
Disc. List	-6%	-12%	On request	

Part number	Housing only	Housing and bearing	For shaft Ød	ØD	A	C	H	A1 ±0,15	C1
SA12	SAKH-12-LL		12	19	40	28	33	29	14
SA16	SAKH-16-LL		16	24	45	30	38	34	15
SA20	SAKH-20-LL		20	28	53	30	45	40	15
SA25	SAKH-25-LL		25	35	62	40	54	48	20
SA30	SAKH-30-LL		30	40	67	50	60	53	25
SA40	SAKH-40-LL		40	52	87	60	76	69	30
SA50	SAKH-50-LL		50	62	103	70	92	82	35

Part number	Housing only	Housing and bearing	H1 +0,010 -0,02	H2	H3	ØM	Ød1	Stock* Housing + bearing	Price each 1 to 4 Housing only	Housing + bearing
SA12	SAKH-12-LL		17	11	16	M5	4,3	✓	35,07 €	49,79 €
SA16	SAKH-16-LL		19	11	18	M5	4,3	✓	36,65 €	55,56 €
SA20	SAKH-20-LL		23	13	22	M6	5,3	✓	40,85 €	61,84 €
SA25	SAKH-25-LL		27	18	26	M8	6,6	✓	51,37 €	74,43 €
SA30	SAKH-30-LL		30	18	29	M8	6,6	✓	67,07 €	98,58 €
SA40	SAKH-40-LL		39	22	38	M10	8,4	-	99,62 €	145,79 €
SA50	SAKH-50-LL		47	26	46	M12	10,5	-	131,12 €	188,83 €

*Depending on availability - Dimensions in mm

Our other products




MFB_MHB
Moulded plastic bevel gear (nylon), 1.5:1



PAV
Fixed anti-vibration foot mount, Vibration-dampening



GMK17_RG
Joint for guiding profile, Rounded



RPP14
RPP heavy duty timing belt, RPP14



SFE
Female rod ends, Stainless steel / PTFE



T10courroie
T type timing belt, T10 Steel cored polyurethane



Q7
Angular contact ball bearing, Steel



TSRTC
Stem support for caster, For swivel caster with central hole




SH0
Parallel axis helical gear, Steel 20NCD2



Q1
Self-aligning radial ball bearing, Steel



DOMI50
Accessories, Fixing kit



KM
Bearing locknut, Locknut KM

Complementary products



SA_SAKH
Housing for linear bearing, Closed - light load



KH
Linear bearing, Light