

Powercoil thread inserts

Stock

PWC

Thread repair


- Thread insert repair kits (with or without insertion tools)
- Single size of insert per kit
- The thread length is 1.5 x the O.D.

Tap

- The taps supplied are designed to be used with thread inserts (STI) and are not compatible with standard metric threads.

Info

- Kits with tools supplied include 1 drill, 1 tap, 1 insertion tool and 1 tang break tool.



DISCOUNTS

Qty	1+	5+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØD	Pitch	L	Ø Drilling	Qty per box	Stock*	Price each 1 to 4
Kit inc installation tools							
PWC-M3/KIT	M3	0,50	4,5	3,2	20	✓	104,10 €
PWC-M4/KIT	M4	0,70	6,0	4,2	20	✓	104,10 €
PWC-M5/KIT	M5	0,80	7,5	5,2	20	✓	104,10 €
PWC-M6/KIT	M6	1,00	9,0	6,3	20	✓	109,71 €
PWC-M8/KIT	M8	1,25	12,0	8,3	20	✓	126,61 €
PWC-M10/KIT	M10	1,50	15,0	10,4	15	-	135,05 €
PWC-M12/KIT	M12	1,75	18,0	12,4	10	-	163,19 €
Wallets without installation tools							
PWC-M3/B	M3	0,50	4,5	3,2	10	✓	8,88 €
PWC-M4/B	M4	0,70	6,0	4,2	10	✓	8,88 €
PWC-M5/B	M5	0,80	7,5	5,2	10	✓	8,88 €
PWC-M6/B	M6	1,00	9,0	6,3	10	✓	8,88 €
PWC-M8/B	M8	1,25	12,0	8,3	10	✓	10,54 €
PWC-M10/B	M10	1,50	15,0	10,4	10	✓	11,92 €
PWC-M12/B	M12	1,75	18,0	12,4	10	✓	17,68 €

Dimensions in mm

Our other products



RFK38C
Hypoid gearbox -
Stainless steel, up to
200 Nm



CHMR75
Worm and wheel gear
reducer, up to 298
Nm



PSG25
Spur gear - precision
range, Stainless steel
303



PAT85
Pressed stainless
steel articulating foot
Ø85, Ø 85



SSB
Stainless steel bevel
gear, 1:1



BPFL
Sheet steel flanged
bearing for light
loads, Sheet steel



FBL6000_K19
Brush strip per meter
horsehair fibres Ø0.2,
Black horsehair



CLM
Male clevis end,
Stainless steel short



CAP805
Slat top chain
stainless steel, Large
range 805



CABtool
Fitting cable tools,
Crimping tools



NKIA
Combined bearing
with inner ring, Axial
load in one direction



PRESS5HR
Manual workbench
press, Force up to
500kg

Complementary products



CHC
Socket headed screw,
Steel class 12.19



CHCSS
Socket headed screw,
Stainless steel - A2



VTH
Hexagonal headed
bolts, Steel class 8.8



SHW
Plain washer, A2
Stainless steel