

Self-aligning radial ball bearing

New

Q1
Q2

Steel

- Self aligning bearing that is unaffected by any errors in alignment
- Static and dynamic loads are radial loads
- Materials:
 - Rings and balls: steel
 - ETN9: Polyamide cage
 - ACC: Steel cage




DISCOUNTS

Qty	1+	4+	8+
Disc.	List	-15%	On request

Part number	Ød	ØD1	B	Load (kN)		Speed (rpm)		Weight (kg)	Price each 1 to 3
				Dynamic (C)	Static (Co)	Grease	Oil		
Q126-ETN9	6	19	6	2,460	0,470	34425	40500	0,009	3,54 €
Q1200-ETN9	10	30	9	5,420	1,160	27540	32400	0,034	3,36 €
Q1201-ETN9	12	32	10	6,120	1,400	24480	28800	0,040	3,51 €
Q2201-ETN9	12	32	14	8,350	1,860	22950	27000	0,053	5,01 €
Q1202-ETN9	15	35	11	7,260	1,720	21420	25200	0,049	3,82 €
Q2202-ETN9	15	35	14	8,540	2,000	19890	23400	0,060	4,46 €
Q2203-ETN9	17	40	12	8,660	2,160	18360	21600	0,073	3,94 €
Q2203-ETN9	17	40	16	10,390	2,500	18360	21600	0,088	4,06 €
Q1204-ETN9	20	47	14	12,450	3,330	15300	18000	0,120	5,59 €
Q2204-ETN9	20	47	18	16,460	4,070	15300	18000	0,140	5,84 €
Q1205-ACC	25	52	15	14,010	3,920	13770	16200	0,140	4,80 €
Q2205-ETN9	25	52	18	16,460	4,310	13770	16200	0,160	8,29 €
Q1305-ETN9	25	62	17	18,620	5,290	11475	13500	0,260	7,61 €
Q2305-ETN9	25	62	24	26,460	6,960	12240	14400	0,340	11,65 €
Q1206-ETN9	30	62	16	15,290	4,560	11475	13500	0,220	7,49 €
Q2206-ETN9	30	62	20	23,320	6,570	11475	13500	0,260	9,27 €
Q1306-ETN9	30	72	19	22,050	6,660	9945	11700	0,390	9,21 €
Q2306-ETN9	30	72	27	30,580	8,620	9945	11700	0,500	14,90 €
Q1207-ETN9	35	72	17	18,620	5,880	9945	11700	0,320	8,38 €
Q2207-ETN9	35	72	23	30,090	8,620	9180	10800	0,400	9,51 €
Q2307-ACC	35	80	21	25,970	8,330	8415	9900	0,510	11,78 €
Q12307-ACC	35	80	31	38,910	10,980	9180	10800	0,680	15,51 €

Dimensions in mm



DISCOUNTS

Qty	1+	4+	8+
Disc.	List	-15%	On request

Part number	Ød	ØD1	B	Load (kN)		Speed (rpm)		Weight (kg)	Price each 1 to 3
				Dynamic (C)	Static (Co)	lubricant Grease	Oil		
Q1208-ETN9	40	80	18	19,500	6,810	8415	9900	0,420	10,40 €
Q2208-ETN9	40	80	23	31,260	9,800	8415	9900	0,510	10,98 €
Q2308-ACC	40	90	33	52,920	15,680	7650	9000	0,930	21,14 €
Q1209-ACC	45	85	19	22,440	7,640	8415	9900	0,470	10,77 €
Q2209-ACC	45	85	23	31,850	10,390	7650	9000	0,550	13,24 €
Q2309-ACC	45	100	36	62,430	18,910	6885	8100	1,250	31,94 €
Q1210-ACC	50	90	20	25,970	8,970	7650	9000	0,530	12,14 €
Q2210-ACC	50	90	23	33,120	10,980	7268	8550	0,600	14,99 €
Q1310-ETN9	50	110	27	42,730	13,720	6120	7200	1,200	25,73 €
Q2310-ACC	50	110	40	62,430	19,600	7268	8550	1,650	39,13 €
Q1211-ETN9	55	100	21	27,050	10,390	6885	8100	0,710	16,18 €
Q2211-ACC	55	100	25	38,220	13,130	6503	7650	0,810	21,05 €
Q1311-ACC	55	120	29	49,690	17,640	5738	6750	1,600	29,49 €
Q2311-ACC	55	120	43	74,580	23,520	5738	6750	2,100	76,04 €
Q1212-ACC	60	110	22	30,580	11,960	6503	7650	0,900	18,48 €
Q2212-ACC	60	110	28	47,820	16,660	6120	7200	1,100	26,46 €
Q1312-ACC	60	130	31	57,330	21,560	4820	5670	1,950	36,19 €
Q2312-ACC	60	130	46	85,360	27,930	5355	6300	2,600	78,30 €
Q1213-ACC	65	120	23	34,400	13,720	5355	6300	1,150	22,12 €
Q2213-ACC	65	120	31	56,060	19,600	5355	6300	1,450	31,97 €
Q2215-ACC	75	130	31	57,330	21,560	4820	5670	1,600	40,51 €
Q2216-ACC	80	140	33	63,700	24,990	4590	5400	2,000	44,43 €
Q2218-ACC	90	160	40	68,800	27,930	4055	4770	3,400	88,40 €

Dimensions in mm

Our other products



CHTRP

Single and dual output gearboxes, Up to 9,1 Nm



J64

Spur gear coaxial gearbox, from 0.57 to 2.25 Nm - Inline



CHA_GC_14SS

Stainless steel garnet hinge, To screw



PGM52-M4

Pull handle, Brass



CHTRB

Single and dual output gearboxes, Up to 53,1 Nm



GLT2-17

Telescopic drawer runners for groove mounting, Partial extension



PTGT

Tensioner pulley, For V belts




WSSss

Symmetrical S shaped hook stainless steel, Stainless steel



M1

Worm and wheel set, Hardened steel



BCM_TP

Modular cylindrical brush, Tampico



GE32

Sprung toggle latch with connecting link,



BMM

Knurled knob - male, Knurled

Complementary products




Q4

Double row radial contact ball bearing, Radial contact - Steel



QTR

Tapered roller bearing, Steel



KM

Bearing locknut, Locknut KM



EAR

Bearing locknut, Self locking locknut - nylon lock washer