


Suction cup threaded insert


Socket screw

SCR
ADAG

- Material: nickel brass




Assembly diagram




Socket screw insert



Adaptor



female



male

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc. List	-5%	-10%	-15%	On request	

Insert socket head

Part number	Ø	H	For suction cup	For adaptor	Stock*	Price each 1 to 49
SCR15M5	M5	9	DFG15	ADAG18M5F	✓	2,21 €
SCR20M5	M5	11	DFG20	ADAG18F5F	✓	3,28 €
SCR30M6	M6	19	DCA33, DCA43, DCG30, DCG40, DCG60	ADAG18F6F, ADAG18M6F	✓	1,85 €
SCR20BM6	M6	14	DFG25, DFG30, DFG40	ADAG14F6F	✓	3,28 €
SCR50M6	M6	17	DFG50	ADAG14M6F	✓	4,59 €

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc. List	-5%	-10%	-15%	On request	

Adaptor

Part number	ØM	H	A/F	For socket screw insert	Stock*	Price each 1 to 49
ADAG18F6F	1/8»	14,0	13	female	-	2,21 €
ADAG14F6F	1/4»	17,5	17	female	-	2,89 €
ADAG18M6F	1/8»	13,0	13	male	✓	2,21 €
ADAG14M6F	1/4»	15,0	17	male	✓	2,21 €
ADAG18M5F	1/8»	13,0	13	male	✓	2,89 €
ADAG18F5F	1/8»	14,0	13	female	-	3,13 €

*Depending on availability - Dimensions in mm

Our other products




HSS

Shoulder screw
ISO7379, Hardened
Steel class 12.9



RCC_RCX

Spherical tilt washer -
DIN6319, concave



LAT4

4A motorised linear
actuator, 4 amperes



HTD8M_50

HTD Heavy duty
timing pulley, HTD8
Steel



CHAsb63

Hinge without pin,
Polymer pin hinge



CTZYSS

Stainless steel diablo
shaped elasto mount,
Stainless steel




SSB

Stainless steel bevel
gear, 1:1



VPPTss

Stainless steel
handwheel with
handle, Stainless steel
304



SLS

Bearing block for
leadscrew, Fixed



NJM

Multiple junction
clamp, Multiple



VDS

Sliding lock
adjustment system,



M1

Worm and wheel set,
Non hardened steel

Complementary products



SCR

Suction cup threaded
insert, Adaptor for
insert



DCG

Suction cup, 2.5
bellows, nitrile