


Single row cylindrical roller bearings

QNUP

One fixed internal flange and one free internal flange

- The external ring has two fixed flanges whereas the internal ring has one fixed and one free flange.
- The axial movement of the shaft is restricted in both directions.
- Static and dynamic loads are radial loads
- Max working temperature: Polyamide cage: 120°C
Steel or brass cage: 150°C
- Materials:
Steel flanges and cylinders
P: polyamide cage
M: solid brass cage
J: pressed steel cage



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List -10%	-15%	-20%	On request	

Part number	Ød	ØD1	B	Load (kN)		Speed (rpm)		Weight (kg)	Price each 1 to 5
				Dynamic (C)	Static (Co)	lubricant	Oil		
QNUP203-M	17	40	12	17	14	16830	19800	0,073	15.15 €
QNUP2203-P	17	40	16	23	21	16830	19800	0,097	25.36 €
QNUP204-P	20	47	14	25	22	14535	17100	0,12	15.87 €
QNUP205-J	25	52	15	28	26	12240	14400	0,14	17.68 €
QNUP2205-M	25	52	18	33	33	12240	14400	0,17	26.94 €
QNUP206-P	30	62	16	43	36	10710	12600	0,22	21.75 €
QNUP2206-J	30	62	20	54	48	10710	12600	0,27	29.34 €
QNUP207-J	35	72	17	55	47	9180	10800	0,32	23.10 €
QNUP2207-P	35	72	23	68	62	9180	10800	0,42	30.78 €
QNUP307-J	35	80	21	74	62	8415	9900	0,51	29.08 €
QNUP2307-J	35	80	31	104	96	8415	9900	0,75	44.20 €
QNUP208-J	40	80	18	61	52	8415	9900	0,4	29.73 €
QNUP2308-J	40	90	33	126	118	7268	8550	0,98	53.86 €
QNUP209-J	45	85	19	68	63	7268	8550	0,45	31.11 €
QNUP210-P	50	90	20	72	68	6885	8100	0,51	31.80 €
QNUP2310-J	50	110	40	182	182	6120	7200	1,8	75.16 €
QNUP211-J	55	100	21	95	93	6120	7200	0,69	35.37 €
QNUP311-P	55	120	29	153	140	5355	6300	1,55	54.55 €
QNUP212-J	60	110	22	106	100	5738	6750	0,86	41.62 €
QNUP213-M	65	120	23	120	116	5126	6030	1,1	47.86 €

Dimensions in mm

Our other products



DOMI30

Connecting kits, XY linking kit



PRF JL2

Lip seal for panel, Door seal - Ø 2mm



PAMF100EB

Articulated foot with sheet metal base Ø100, Articulated foot



GLB

Small 6 lobe threaded handle - female, Technopolymer - Stainless steel



VAP

Magnetic stud with central hole, With central hole



EHD12

Internal epicyclic servo reducers, from 60 to 140 Nm



PCS_PA6

Plastic sprocket, 12.7mm (DIN 08B-1)




CDPC

Flanged drill bushing, Steel



NPTR10

Adjustable cross clamp, Adjustable



M2

Worm and wheel set, Machined plastic



PMC150_M16

Anti-vibration machine mount,



INO

Internal gear, Steel 20NCD2

Complementary products




Q1

Self-aligning radial ball bearing, Steel



NKX

Combined bearing without inner ring, Needle and ball bearings



KM

Bearing locknut, Locknut KM



EAR

Bearing locknut, Self locking locknut - nylon lock washer