

# Steel index bolt



## SLB


## Pull to unlock

- **Manual indexing bolt**
- Exists in 4 different versions
- **Materials:**
  - Bolt: Glass reinforced polyamide
  - Body: Blackened steel (class 5.8)
  - Tip: Hardened steel
  - Spring: Steel
- Working temp: -50°C to +130°C




### Uses

- Locating and indexing
- Pull to retract locking pin.
- Turn through 90° to retain (Models C + D)



Normal

Retracted



**MODEL A**  
Without lock nut  
Without slot

**MODEL B**  
With lock nut  
Without slot

**MODEL C**  
Without lock nut  
With slot

**MODEL D**  
With lock nut  
With slot

### DISCOUNTS

Qty	1+	6+	20+
Disc.	List -10%	On request	

Part number	D	D1	D2	L	L1	L2	L3	H	SW1	SW2	F x 30°	Spring strength		Price each 1 to 5	
												initial F1 (N)	final F2 (N)		
SLB10-A	5	M10x1,0	21	47	17	7	15	5	13	-	1,3	5	12	✓	11,36 €
SLB10-B	5	M10x1,0	21	47	17	7	15	5	13	17	1,3	5	12	✓	11,73 €
SLB10-C	5	M10x1,0	21	47	17	7	15	5	13	-	1,3	5	12	✓	14,37 €
SLB10-D	5	M10x1,0	21	47	17	7	15	5	13	17	1,3	5	12	✓	14,50 €
SLB12-A	6	M12x1,5	25	56	20	8	17	6	14	-	1,8	6	14	✓	12,67 €
SLB12-B	6	M12x1,5	25	56	20	8	17	6	14	19	1,8	6	14	✓	13,05 €
SLB12-C	6	M12x1,5	25	56	20	8	17	6	14	-	1,8	6	14	✓	15,92 €
SLB12-D	6	M12x1,5	25	56	20	8	17	6	14	19	1,8	6	14	✓	16,33 €
SLB16-A	8	M16x1,5	33	74	26	10	23	8	19	-	2,3	15	35	✓	16,33 €
SLB16-B	8	M16x1,5	33	74	26	10	23	8	19	24	2,3	15	35	✓	17,43 €
SLB16-C	8	M16x1,5	33	74	26	10	23	8	19	-	2,3	15	35	✓	19,07 €
SLB16-D	8	M16x1,5	33	74	26	10	23	8	19	24	2,3	15	35	✓	20,16 €
SLB20-A	10	M20x1,5	33	80	28	12	25	10	22	-	2,8	15	40	✓	23,62 €
SLB20-B	10	M20x1,5	33	80	28	12	25	10	22	30	2,8	15	40	✓	24,73 €
SLB20-C	10	M20x1,5	33	80	28	12	25	10	22	-	2,8	15	40	✓	30,92 €
SLB20-D	10	M20x1,5	33	80	28	12	25	10	22	30	2,8	15	40	✓	32,00 €


\*Depending on availability - Dimensions in mm

## Our other products



SLHVlok

Horizontal toggle clamp, Horizontal toggle clamp / vertical foot



TBV

Manual lifting tables, 3kg



CDPC

Flanged drill bushing, Steel



SHA

Handwheel without handle, Polyamide



KKSS

Rounded end feather key, Stainless steel



PRES3HR

Manual workbench press, Force up to 400kg



CHA135

Screwed hinge, 135 degrees



BTE

Universal tension arm, For normal applications



PO

Pull handle - Multi-sector, Tapped recessed insert



FB\_ECO

Eco. range steel bevel gear, 4:1



GE\_ES

Spherical bushing, Steel / steel



SVT5

Screwjack with travelling screw, with translating screw

## Complementary products



SLBE

Indexing plunger - Spacer, Spacer for SLB and SLBS index bolts