

# Spacer for index bolt

## SLBE

## Used with SLB and SLBS



- Allows the length of the thread of index bolts to be adapted to the length required for an application (wall thickness)
- Material:  
stainless steel, natural finish

### Accessories

- Used with SLB and SLBS index bolts  
SLB and SLBS

### Info

- Not sold individually,  
contact us for details



### DISCOUNTS

Qty	1+	40+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	ØD	ØD1	Length L (mm)	Weight (kg)	Price each 1 to 39
SLBE8-11-2/SS	8	11	2	0,6	0,59 €
SLBE8-11-3/SS	8	11	3	0,9	0,62 €
SLBE8-11-4/SS	8	11	4	1,3	0,68 €
SLBE8-11-6/SS	8	11	6	2,0	0,72 €
SLBE8-11-8/SS	8	11	8	2,6	0,78 €
SLBE10-14-2/SS	10	14	2	1,1	0,62 €
SLBE10-14-3/SS	10	14	3	1,7	0,72 €
SLBE10-14-4/SS	10	14	4	2,2	0,72 €
SLBE10-14-6/SS	10	14	6	3,4	0,78 €
SLBE10-14-8/SS	10	14	8	4,5	0,87 €
SLBE12-15-2/SS	12	15	2	0,9	0,68 €
SLBE12-15-4/SS	12	15	4	1,9	0,78 €
SLBE12-15-5/SS	12	15	5	2,4	0,84 €
SLBE12-15-6/SS	12	15	6	2,8	0,87 €
SLBE12-15-8/SS	12	15	8	3,8	0,97 €
SLBE12-17-2/SS	12	17	2	1,6	0,78 €
SLBE12-17-4/SS	12	17	4	3,4	0,87 €
SLBE12-17-5/SS	12	17	5	4,3	0,97 €
SLBE12-17-6/SS	12	17	6	5,2	1,00 €
SLBE12-17-8/SS	12	17	8	6,9	1,08 €
SLBE16-21-4/SS	16	21	4	4,4	1,00 €
SLBE16-21-5/SS	16	21	5	5,5	1,08 €
SLBE16-21-6/SS	16	21	6	6,6	1,17 €
SLBE16-21-8/SS	16	21	8	8,8	1,26 €
SLBE16-21-10/SS	16	21	10	11,0	1,32 €

Dimensions in mm

## Our other products



HFL

One way needle bearing, Needle bearing



GP

Spring loaded toggle latch, Standard



PO

Pull handle - Multi-sector, Tapped recessed insert



PLC\_PLT

Magnetic stud with central hole, With central hole



PSG3S

Spur gear - precision range, Stainless steel 316



UGPC

Actuator guide kit, Short bearing



TAC\_SS

Stainless steel rigging screw (hook/eye), Stainless steel



CHML40

Worm and wheel gear reducer, up to 57 Nm - Integrated torque limiter



PTA80ssEB

Articulated foot with sheet metal base Ø80, Articulated foot



CHTRP

Single and dual output gearboxes, Up to 28,8 Nm



DB

Steel bevel gear, 2:1



DOG258

Motor-gearbox 12V and 24V DC, from 12 to 15 Nm

## Complementary products



SLB

Indexing plunger, steel class 5.8



SLB

Indexing plunger, steel class 5.8



SLB

Indexing plunger, steel class 5.8



SLB

Indexing plunger, steel class 5.8