





- Support for RFK gearboxes
- Inward or outward facing
- Sold in pairs
- Material:  
316 stainless steel



Brackets facing inwards



Brackets facing outwards

### DISCOUNTS

Qty	1+	2+	4+
Rem.	Net	-5%	On request

Part N°	H	H1	V	V1	V2	V3	V4	X	E	F
RFK28-FP/SS	80	136,85	93	129	110	70	51	80	8,5	3
RFK38-FP/SS	90	154,50	114	157	135	85	63	100	8,5	4
RFK48-FP/SS	95	169,50	124	170	148	90	68	120	11,5	5
RFK58-FP/SS	110	198,00	144	204	178	100	74	140	13,0	5

Part N°	L1 for flange				Price each
	63B5	71B14	80B14	90B14	
RFK28-FP/SS	65,5	72,5	92,5	92,5	81,95 €
RFK38-FP/SS	67,0	74,0	94,0	94,0	104,72 €
RFK48-FP/SS	78,5	85,5	105,5	105,5	129,30 €
RFK58-FP/SS	85,0	92,0	112,0	112,0	161,17 €

All dimensions in mm

## Our other products



PRF4590  
Standard aluminium profile, 45 x 90 mm




CHALss  
Piano hinge, Stainless steel



SCA\_SS  
Stainless steel flat cable clamp, Stainless steel



NPTF30  
Fixed tube carrier, Fixed Ø14 to Ø20



KM  
Bearing locknut, Locknut KM



F7-SF-SM  
Multifunction display, Mounting bracket for front mounting



BABss  
303 Stainless steel ball pin, 303 Stainless steel



PW\_PWG3  
Worm - precision range, Stainless steel



PRF4545\_P  
Stripp Aluminium profile with extendable slot, 45 x



SBF  
Sealed flange bearing unit for Food Industry, cover



PW\_PWG15  
Worm - precision range, Stainless steel



NCT  
Square tube connector, Fixed angle

## Complementary products



RFK28C  
Hypoid gearbox - Stainless steel, up to 130 Nm



RFK38B  
Hypoid gearbox - Stainless steel, up to 200 Nm



RFK38C  
Hypoid gearbox - Stainless steel, up to 200 Nm



RFK48B  
Hypoid gearbox - Stainless steel, up to 350 Nm