

Stainless steel Worm and wheel motorgearbox

Create your set

For food industry

Supporting feet **RFV-FP**
(tome 2 p.326)

Protective cover closed
RFV-CAP (tome 2 p.327)

Motor 0,18kW à 1,5kW
(tome 2 p.318)

Gear reducer **RFV40, RFV50, RFV63**,
Reduction ratio of 7,5/1 to 100/1,
3 flanges to choose depending
on the motor selected

RFV-CAP protective cover
(tome 2 p.327)
open or closed to prevent
material retention in the output
bore

Reaction arm **RFV-BR**
(tome 2 p.325) to better
support the load

* See data sheet (tome 2 p.328)

Stainless steel protective cover


Stock

RFV-CAP


Worm and wheel gearbox

- Protective cover to prevent dirt etc from lodging in output shaft
- For full protection, use one cover on each side of the gearbox
- Material:
316 stainless steel

Suitable for the food industry



Closed cover RFV-CAP-F



Open cover RFV-CAP-AT

DISCOUNTS

Qty	1+	2+	4+
Disc.	List -5%	On request	

Part number	ØE	ØP	ØD	B	A	S	N	Price each
Closed cover								
RFV40-CAP-F/SS	90	60	-	20,0	56,5	75	6,5	32,10 €
RFV50-CAP-F/SS	100	70	-	20,5	64,0	85	8,5	39,60 €
RFV63-CAP-F/SS	110	80	-	26,0	79,0	95	8,5	47,11 €
Open cover for transversal shaft								
RFV40-CAP-AT/SS	90	60	18	17,0	53,5	75	6,5	35,32 €
RFV50-CAP-AT/SS	100	70	25	17,0	60,5	85	8,5	41,74 €
RFV63-CAP-AT/SS	110	80	25	22,0	75,0	95	8,5	49,25 €

Dimensions in mm