


## Stainless steel 304L

Ratio  
**2:1**  
**3:1**  
**4:1**

- Module 0.8 to 2.5
- Teeth Gleason
- Material:  
stainless steel 304L
- Pressure angle 20°



stainless steel

TORQUE AND POWER INDICATION	For 20 teeth at 1000 rpm					
	2.5 MOD	2.0 MOD	1.5 MOD	1.25 MOD	1.0 MOD	0.8 MOD
Torque (Nm)	4.30	2.20	0.94	0.71	0.57	0.14
Power (kW)	0.455	0.231	0.097	0.08	0.03	0.015

### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	Teeth		Z	Module	ØP	E	ØD	ØA	ØM	F	G	H	Screw		Price each 1 to 5
	R	T													
SSDB0.8-15	15	0,8	12,00	20,00	13,93	6	10	11,90	7,50	4,02	M3	3,50	46,73	€	
SSDB0.8-30	30		24,00	14,00	24,64	8	20	10,08	5,50	4,02	M3	3,50	55,09	€	
SSDB1-15	15	2:1	15,00	24,00	17,42	8	14	13,87	8,76	5,03	M4	4,00	52,99	€	
SSDB1-30	30		30,00	18,00	30,58	10	25	13,11	7,00	5,03	M4	4,00	65,15	€	
SSDB1.5-15	15	1,5	22,50	35,00	26,12	10	21	19,84	12,13	7,55	M4	5,00	57,68	€	
SSDB1.5-30	30		45,00	27,00	45,87	10	30	19,66	11,00	7,55	M4	5,00	74,05	€	
SSDB2-15	15	2	30,00	45,00	34,83	12	28	24,76	14,86	10,06	M5	7,50	63,95	€	
SSDB2-30	30		60,00	35,00	61,16	12	40	25,21	14,00	10,06	M5	8,00	88,65	€	
SSDB2.5-15	15	2,5	37,50	54,00	43,54	15	32	29,51	16,51	13,53	M5	8,00	87,37	€	
SSDB2.5-30	30		75,00	41,50	76,45	15	30	29,31	13,31	13,53	M5	7,00	121,37	€	
SSTB0.8-15	15	0,8	12,00	28,00	14,14	6	10	15,63	9,67	5,69	M3	5,00			
SSTB0.8-45	45		36,00	20,00	36,30	8	28	16,07	8,00	5,69	M3	4,00			
SSTB1-15	15	3:1	15,00	32,00	17,67	8	13	16,54	9,18	7,12	M4	4,50			
SSTB1-45	45		45,00	24,00	45,37	10	40	19,09	10,00	7,12	M4	5,00			
SSTB1.5-15	15	1,5	22,50	45,00	26,51	10	18	21,80	10,51	10,67	M4	5,00			
SSTB1.5-45	45		67,50	32,00	68,06	15	50	24,63	12,00	10,67	M4	6,00			
SSFB0.8-15	15	0,8	12,00	35,00	14,23	6	10	18,07	10,58	7,10	M3	5,00			
SSFB0.8-60	60		48,00	20,00	48,22	8	30	15,98	8,00	7,10	M3	4,00			
SSFB1-15	15	4:1	15,00	45,00	17,79	8	13	24,22	14,73	9,28	M4	7,00			
SSFB1-60	60		60,00	30,00	60,27	10	40	25,08	12,00	9,28	M4	6,00			
SSFB1.5-15	15	1,5	22,50	60,00	26,69	10	18	28,82	12,08	13,91	M4	6,00			
SSFB1.5-60	60		60,00	35,00	90,41	15	50	27,61	12,00	13,91	M4	6,00			

Dimensions in mm

On request

## Our other products



DOG111

Motor-gearbox 12V and 24V DC, from 1.5 to 6 Nm



TBD

Manual leadscrew table with opposing threads, 40kg



T5M T10M

T type timing belt per metre, T5 Steel cored polyurethane



DOMI80

Accessories, Fixing kit



GP

Spring loaded toggle latch, Standard



VTH

Hexagonal headed bolts, Steel class 8.8



PNA

PERIFLEX® elastic coupling, Complete coupling



H2

Crossed helical gear crossed axis at 90°, Steel 20NCD2



M1

Worm, Non hardened steel



PSG125

Spur gear - precision range, Pre-hardened Steel 35NCD6



MSP3815

Masterplate® glueable insert rectangular,



HTD8M\_20

HTD Heavy duty timing pulley, HTD8 Steel

## Complementary products



DB

Steel bevel gear, 2:1



ZDB

Machined plastic bevel gear, 2:1