

RGS Couplings for servo-motors

Torque: **0.5 to 190Nm**



- No-wear elastic couplings
- No maintenance
- Low inertia and reduced size
- Easy blind assembly using standard screws
- Dampens vibration
- Electrically insulated

Definition

- TKN Nominal torque (Nm)
- TKMAX Max. torque (Nm)

Info

- Delivered not assembled



 **STANDARD BORE IN STOCK**

DISCOUNTS

Qty	1+	5+	10+	25+
Disc.	List	-6%	-12%	On request

Transmissible torque (Nm) by friction for split hub

Part number	Ø3	Ø4	Ø5	Ø6	Ø7	Ø8	Ø10	Ø12	Ø14	Ø15	Ø16	Ø19	Ø20	Ø24	Ø28	Ø30	Ø32
RGS-AL-5	-	-															
RGS-AL-7		0,65	0,70	0,74	0,79												
RGS-AL-9		1,48	-	1,43	-	1,79	1,94										
RGS-AL-14			3,32	3,43	-	3,67	3,91	4,14	4,38								
RGS-AL-19							18,90	-	20,80	21,3	21,7	-	23,6				
RGS-AL-24												27,5	28	29,0	31		
RGS-AL-28														62,0	66	69	71 73

Part number	Max. speed (rpm)	Torsional stiffness		Radial stiffness (N/mm)	Torque (Nm)			Misalignment		
		static (Nm/rad)	dynamic (Nm/rad)		T_{KSP}	T_{KN}	T_{KMAX}	axial (mm)	radial (mm)	angular
RGS-AL-5	38 000	5,16	16	154	0,08	0,50	1,00	+0,4/-0,2	0,06	1°
RGS-AL-7	27 000	14,30	43	219	0,20	1,20	2,40	+0,6/-0,3	0,10	1°
RGS-AL-9	19 000	31,50	95	262	0,45	3,00	6,00	+0,8/-0,4	0,13	1°
RGS-AL-14	127 000	114,60	344	336	1,00	7,50	15,00	+1/-0,5	0,15	1°
RGS-AL-19	9 550	1090,00	1720	1120	2,50	12,00	24,00	+1,2/-0,5	0,10	1°
RGS-AL-24	6 950	2280,00	4010	1480	-	35,00	70,00	+1,4/-0,5	0,14	1°
RGS-AL-28	5 850	4080,00	6754	1780	-	95,00	190,00	+1,5/-0,7	0,15	1°



Dimensions in mm

Characteristics

- Long-life
- Fixed by clamping jaw (except RGS-AL-5)
- Single-slit split hub (except RGS-AL-24 and RGS-AL-28 double slit)
- Preconstrained raised coupling
- Working temperature: -40°C to $+90^{\circ}\text{C}$ (occasional -50°C to $+120^{\circ}\text{C}$)
- Materials:
 - Hub: aluminium
 - Ring: polyurethane elastic (92 Shore A)

Uses

- Measuring and control instruments
- Servo-control, ball-screw systems
- Machine tools



DISCOUNTS

Qty	1+	5+	10+	25+
Disc.	List	-6%	-12%	On request

Part number	Clamping screw			Tightening torque T_A (Nm)
	M_1	t_1	$\text{Ø}D_K$	
RGS-AL-5	M1,2	2,5	11,4	-
RGS-AL-7	M2,0	3,5	16,5	0,37
RGS-AL-9	M2,5	5,0	23,4	0,76
RGS-AL-14	M3,0	5,0	32,2	1,34
RGS-AL-19	M6,0	12,0	45,7	10,50
RGS-AL-24	M6,0	10,5	56,4	10,50
RGS-AL-28	M8,0	11,5	72,6	25,00

Part number	Standard bore									Price each 1 to 4
	$\text{Ø}A$ (H7)	D_H	d_H	L	$L_1;L_2$	E	b	s	f	
RGS-AL-5	Plein	10	-	15	5	5	4	0,5	4,0	40,38 €
RGS-AL-7	4, 5, 6, 7	14	-	22	7	8	6	1,0	6,0	68,24 €
RGS-AL-9	4, 6, 8, 10	20	7,2	30	10	10	8	1,0	1,5	68,71 €
RGS-AL-14	5, 6, 8, 10, 12, 14	30	10,5	35	11	13	10	1,5	2,0	76,80 €
RGS-AL-19	10, 14, 15, 16, 20	40	18,0	66	25	16	12	2,0	3,0	178,90 €
RGS-AL-24	16, 19, 20, 24, 25	55	27,0	78	30	18	14	2,0	3,0	214,29 €
RGS-AL-28	20, 24, 25, 28, 30, 32	65	30,0	90	35	20	15	2,5	4,0	279,92 €


Dimensions in mm

Our other products



MAX22

Motor-gearbox 12V and 24V DC, from 0,07 to 0,2Nm



BETASS

Hitch pin, Hitch



STRIP

Sealing brush strip, 3m length



DOMI30

Connecting kits, XZ linking kit



DH

Dowel pin, Solid DIN 6325



G0

Steel spur gear, Steel 20NCD2



AC144

Strike for toggle latch, 22mm




S_ZZ

Deep groove ball bearing, Stainless steel



PTKFss

Fixable foot for the food industry, Stainless steel - 3-A



IN2

Internal gear, Machined plastic (delrin)



CM

Tools Hygienic Usit® and Hygienic Design®,



PSG2

Spur gear - precision range, Case hardened steel 20NCD2

Complementary products



DKGS

Backlash free coupling Gerwah®, from 0.5 to 3Nm



EKGS

Backlash free coupling Gerwah®, from 0.5 to 35Nm



RTE

Rotex®, jaw coupling, Aluminium