

High Temperature Castors



RHTPLSS

Load up to 200kg

- **High temperature industrial castor**
- Swivel system on 2 crowns of balls
- Double-locking swivel castor:
use the foot pedal to lock and unlock.
- Slide bearings
- Materials:
304 stainless steel sheet
Polyamide wheel (see RHT)
- Working temp.: -30°C to +280°C



Fixed



Swivel

Advantages

- Large storage capacity
- Resists high temperatures



Double locking swivel



ØD



B



H



L



M



T



ØK

DISCOUNTS

Qty	1+	5+	15+
Disc. Price	-5%	On request	

Part number	ØD	B	H	L	M	ØT	Circle interference ØK	Load maximum (kg)	Price per unit 1 to 4
Fixed									
RHT80/PL/F/SS	80	35	105	115x83	80x60	11x9		125	32,70 €
RHT100/PL/F/SS	100	35	126	115x83	80x60	11x9		150	33,33 €
RHT125/PL/F/SS	125	40	153	115x83	80x60	11x9		200	76,05 €
Swivel									
RHT80/PL/P/SS	80	35	105	115x83	80x60	11x9	173	125	40,77 €
RHT100/PL/P/SS	100	35	126	115x83	80x60	11x9	193	150	41,93 €
RHT125/PL/P/SS	125	40	153	115x83	80x60	11x9	221	200	85,28 €
Double locking swivel									
RHT80/PL/PDB/SS	80	35	105	115x83	80x60	11x9	293	125	49,34 €
RHT100/PL/PDB/SS	100	35	126	115x83	80x60	11x9	293	150	50,50 €
RHT125/PL/PDB/SS	125	40	153	115x83	80x60	11x9	293	200	93,85 €

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



HK

Manual locking clamp,
Manual locking clamp
T




CMM

Male rod ends DIN
ISO12240-4, Steel /
bronze



BOX-NINA

Self locking nut -
DIN985, Box set of
steel nuts



PO

Pull handle - Multi-
sector, Smooth hole
steel



PSG05

Spur gear - precision
range, Case hardened
steel 20NCD2



NK27

Drylin®N miniature
guiding system, Width
27 mm



P55

Worm and wheel gear
reducer, up to 57 Nm



BAG

Steel Clamping collar,
Steel



BOX-TOR-MAX

Box set of Nitrile O-
rings in nitrile, 2.90 x
1.78mm to 82.14 x



UTKpwc

Utilittrak® 3 wheels
carriage, Polymer
series V wheels



MFB

Flexible bellows
coupling, Aluminium
and Bronze - With set



HK

Manual locking clamp,
Manual locking clamp
LWL

Complementary products



RHTtcss

High Temperature
Castor, up to 200kg



RHTtcss

High Temperature
Castor, up to 200kg



RHT

High Temperature
wheel, up to 200kg



RHTplss

High Temperature
Castor, up to 200kg