

# High Temperature Castors



## RHTPLSS

## Load up to 200kg

- **High temperature industrial castor**
- Swivel system on 2 crowns of balls
- Double-locking swivel castor:  
use the foot pedal to lock and unlock.
- Slide bearings
- Materials:  
304 stainless steel sheet  
Polyamide wheel (see RHT)
- Working temp.: -30°C to +280°C



Fixed



Swivel

### Advantages

- Large storage capacity
- Resists high temperatures



Double locking swivel



ØD



B



H



L



M



T



ØK

### DISCOUNTS

Qty	1+	5+	15+
Disc. Price	-5%	On request	

Part number	ØD	B	H	L	M	ØT	Circle interference ØK	Load maximum (kg)	Price per unit 1 to 4
<b>Fixed</b>									
RHT80/PL/F/SS	80	35	105	115x83	80x60	11x9		125	32,70 €
RHT100/PL/F/SS	100	35	126	115x83	80x60	11x9		150	33,33 €
RHT125/PL/F/SS	125	40	153	115x83	80x60	11x9		200	76,05 €
<b>Swivel</b>									
RHT80/PL/P/SS	80	35	105	115x83	80x60	11x9	173	125	40,77 €
RHT100/PL/P/SS	100	35	126	115x83	80x60	11x9	193	150	41,93 €
RHT125/PL/P/SS	125	40	153	115x83	80x60	11x9	221	200	85,28 €
<b>Double locking swivel</b>									
RHT80/PL/PDB/SS	80	35	105	115x83	80x60	11x9	293	125	49,34 €
RHT100/PL/PDB/SS	100	35	126	115x83	80x60	11x9	293	150	50,50 €
RHT125/PL/PDB/SS	125	40	153	115x83	80x60	11x9	293	200	93,85 €

Dimensions in mm

**HPC**

WEB  
04/2020


www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

## Our other products



DEP  
Tools Hygienic Usit® and Hygienic Design®, Protective insert for s...



T0  
Torsion spring, Stainless steel



BDM  
Pin for magnetic bush, Fast and light magnetic locking



GSA\_A  
Adjustable gas spring, Steel



PLM-C  
Flat gripping magnet, Flat holding magnet




ESCON  
Speed controller 5A accessories, USB cable for PC link



CHM90  
Worm and wheel gear reducer, up to 540 Nm



CDPC  
Flanged drill bushing, Steel



LRH  
Bi-directional leadscrew, Bi-



M  
Bellows cover, Accessory:



WW16  
Drylin® W slide, slide assembly



BAG  
Steel Clamping collar, Steel

## Complementary products



RHTtcss  
High Temperature Castor, up to 200kg



RHTtcss  
High Temperature Castor, up to 200kg



RHT  
High Temperature wheel, up to 200kg



RHTplss  
High Temperature Castor, up to 200kg