


# Self-centering clamping hub steel

## SUP

## Without locknut

- Hexagonal clamping hub
- Effective for all types of shaft-pinion assemblies such as sprocket wheels, gear wheels, pulleys, cams etc..
- Materials:
  - External part: galvanised steel
  - Internal part: nickel-plated steel
  - Nut: nickel-plated steel

**NEW!**




**Reduced installation time**

### Benefits

- Self-centering
- Reduced installation time

### Info

- $T_A$  : Tightening torque of the nut
- $M$  : Transferable torque
- $F_A$  : Transmissible axial load
- $P_W$  : Surface pressure of the shaft
- $P_N$  : Hub surface pressure



### Accessory

- Assembly tool SUP/TOOL (cat. 2 p.130)

### DISCOUNTS

Qty	1+	6+	10+
Disc.	Price	-5%	On request

Part number	ØD1	ØD2	L1	L2	SW	$T_A$	$M$	$F_A$	$P_W$	$P_N$	Weight (g)	Price each
						max. (Nm)	max. (Nm)	max. (kN)	max. (N/mm <sup>2</sup> )	max. (N/mm <sup>2</sup> )		
SUP-005	5	14	19	15	14	9,9	10,1	4,0	264	96	20	✓ 29,66 €
SUP-006	6	14	19	15	14	9,9	12,1	4,0	220	96	19	✓ 29,66 €
SUP-008	8	16	22	17	16	16,9	23,4	5,8	179	91	26	✓ 30,86 €
SUP-009	9	20	24	19	22	34,9	43,7	9,7	245	115	47	- 32,04 €
SUP-010	10	20	24	19	22	34,9	48,6	9,7	221	115	46	✓ 32,82 €
SUP-011	11	22	24	19	22	43,8	59,9	10,9	225	117	51	- 34,81 €
SUP-012	12	22	24	19	22	43,8	65,3	10,9	206	117	49	✓ 35,60 €
SUP-014	14	26	28	22	27	65,0	93,0	13,3	178	99	83	✓ 38,75 €
SUP-015	15	26	28	22	27	65,0	99,0	13,3	166	99	75	✓ 38,75 €
SUP-016	16	26	28	22	27	65,0	106,0	13,3	156	99	73	✓ 38,75 €
SUP-018	18	35	36	27	36	161,0	223,0	24,8	224	125	201	- 42,31 €
SUP-019	19	35	36	27	36	161,0	235,0	24,8	212	125	189	- 41,25 €
SUP-020	20	35	36	27	36	161,0	248,0	24,8	201	125	186	✓ 42,31 €
SUP-022	22	42	41	30	46	250,0	349,0	31,8	197	110	346	✓ 46,57 €
SUP-024	24	42	41	30	46	250,0	381,0	31,8	180	110	326	- 46,57 €
SUP-025	25	42	41	30	46	250,0	397,0	31,8	173	110	315	✓ 46,57 €
SUP-028	28	47	44	33	50	355,0	565,0	40,4	174	110	403	- 53,51 €
SUP-030	30	47	44	33	50	355,0	605,0	40,4	162	110	378	✓ 54,77 €
SUP-032	32	55	51	38	55	490,0	764,0	47,8	166	102	632	- 65,16 €
SUP-035	35	55	51	38	55	490,0	836,0	47,8	151	102	571	✓ 65,16 €
SUP-038	38	62	58	43	65	720,0	1179,0	62,1	159	111	897	- 84,94 €
SUP-040	40	62	58	43	65	720,0	1241,0	62,1	151	111	842	- 84,94 €

Dimensions in mm


**NEW!**

- Hexagonal clamping hub
- Effective for all types of shaft-pinion assemblies such as sprocket wheels, gear wheels, pulleys, cams etc..
- Materials:
  - External part: galvanised steel
  - Internal part: nickel-plated steel
  - Nut: nickel-plated steel

### Benefits


- Self-centering
- Reduced installation time
- The hexagonal locknut makes it easier to lock the shaft-pinion assembly if freely rotating shafts.

**Easier locking**



### Info

- T<sub>A</sub> : Tightening torque of the nut
- M : Transferable torque
- F<sub>A</sub> : Transmissible axial load
- P<sub>w</sub> : Surface pressure of the shaft
- P<sub>N</sub> : Hub surface pressure



### Accessory

- Assembly tool SUP/TOOL (cat. 2 p.130)

### DISCOUNTS

Qty	1+	6+	10+
Disc.	Price	-5%	On request

Part number	ØD1	ØD2	L1	L2	L3	SW	T <sub>A</sub>	M	F <sub>A</sub>	P <sub>w</sub>	P <sub>N</sub>	Weight (g)	Price each
							max. (Nm)	max. (Nm)	max. (kN)	max. (N/mm <sup>2</sup> )	max. (N/mm <sup>2</sup> )		
SUP-005/CC	5	12	19	15	9	14	9,9	10,1	4,0	264	119	18	- 35,11 €
SUP-006/CC	6	12	19	15	9	14	9,9	12,1	4,0	220	119	17	- 33,83 €
SUP-008/CC	8	14	22	17	11	16	16,9	23,4	5,8	179	121	23	- 35,60 €
SUP-009/CC	9	18	24	19	12	22	34,9	43,7	9,7	245	127	47	- 36,88 €
SUP-010/CC	10	18	24	19	12	22	34,9	48,6	9,7	221	127	46	- 37,87 €
SUP-011/CC	11	20	24	19	12	22	43,8	59,9	10,9	225	128	47	- 40,24 €
SUP-012/CC	12	20	24	19	12	22	43,8	65,3	10,9	206	128	45	- 41,25 €
SUP-014/CC	14	24	28	22	15	27	65,0	93,0	13,3	178	107	78	- 45,49 €
SUP-015/CC	15	24	28	22	15	27	65,0	99,0	13,3	166	107	75	- 45,49 €
SUP-016/CC	16	24	28	22	15	27	65,0	106,0	13,3	156	107	70	- 45,49 €
SUP-018/CC	18	30	36	27	17	36	161,0	223,0	24,8	224	145	179	- 50,83 €
SUP-019/CC	19	30	36	27	17	36	161,0	235,0	24,8	212	145	169	- 49,44 €
SUP-020/CC	20	30	36	27	17	36	161,0	248,0	24,8	201	145	213	- 50,83 €
SUP-022/CC	22	38	41	30	20	46	250,0	349,0	31,8	197	122	341	- 57,36 €
SUP-024/CC	24	38	41	30	20	46	250,0	381,0	31,8	180	122	320	- 57,36 €
SUP-025/CC	25	38	41	30	20	46	250,0	397,0	31,8	173	122	310	- 57,36 €
SUP-028/CC	28	42	44	33	23	50	355,0	565,0	40,4	174	123	370	- 63,60 €
SUP-030/CC	30	42	44	33	23	50	355,0	605,0	40,4	162	123	348	- 65,16 €
SUP-032/CC	32	50	51	38	28	55	490,0	764,0	47,8	166	112	555	- 77,24 €
SUP-035/CC	35	50	51	38	28	55	490,0	836,0	47,8	151	112	501	- 77,24 €

Dimensions in mm

## SUP<sub>SS</sub>

## Without locknut

- **Hexagonal clamping hub**
- Effective for all types of shaft-pinion assemblies such as sprocket wheels, gear wheels, pulleys, cams etc..
- **Materials**  
 External part: nickel-plated stainless steel  
 Internal part: nickel-plated stainless steel  
 Nut: stainless steel, hardened and nickel-plated

**NEW!**



**stainless steel**

**Reduced installation time**

### Benefits



- Self-centering
- Reduced installation time

### Info

- $T_A$  : Tightening torque of the nut
- $M$  : Transferable torque
- $F_A$  : Transmissible axial load
- $P_W$  : Surface pressure of the shaft
- $P_N$  : Hub surface pressure

### Accessory

- Assembly tool SUP/TOOL (cat. 2 p.130)



### DISCOUNTS

Qty	1+	2+	5+
Disc.	Price	-5%	On request

Part number	ØD1	ØD2	L1	L2	SW	$T_A$	$M$	$F_A$	$P_W$	$P_N$	Weight	Price each	
						max. (Nm)	max. (Nm)	max. (kN)	max. (N/mm <sup>2</sup> )	max. (N/mm <sup>2</sup> )			
SUP-006/SS	6	14	19	15	14	7	8,5	2,8	154	67	19	-	77,42 €
SUP-008/SS	8	16	22	17	16	12	16,4	4,1	125	64	26	-	77,42 €
SUP-010/SS	10	20	24	19	22	24	34,0	6,8	155	81	46	-	88,22 €
SUP-012/SS	12	22	24	19	22	31	45,7	7,6	144	82	49	-	88,12 €
SUP-016/SS	16	26	28	22	27	46	74,2	9,3	109	69	73	-	97,40 €
SUP-020/SS	20	35	36	27	36	113	173,6	17,4	141	88	186	-	114,60 €
SUP-025/SS	25	42	41	30	46	175	277,9	22,3	121	77	315	-	138,13 €
SUP-030/SS	30	47	44	33	50	249	423,5	28,3	113	77	378	-	138,03 €

Dimensions in mm

With lock nut

SUPccss

**NEW!**

- Hexagonal clamping hub
- Effective for all types of shaft-pinion assemblies such as sprocket wheels, gear wheels, pulleys, cams etc..
- Materials:
  - External part: nickel-plated stainless steel
  - Internal part: nickel-plated stainless steel
  - Nut: stainless steel, hardened and nickel-plated



stainless steel

## Benefits

- Self-centering
- Reduced installation time
- The hexagonal locknut makes it easier to lock the shaft-pinion assembly if freely rotating shafts.



## Info

- $T_A$  : Tightening torque of the nut
- $M$  : Transferable torque
- $F_A$  : Transmissible axial load
- $P_w$  : Surface pressure of the shaft
- $P_n$  : Hub surface pressure

Easier locking

## Accessory

- Assembly tool SUP/TOOL (cat. 2 p.130)



## DISCOUNTS

Qty	1+	2+	5+
Disc.	Price	-5%	On request

Part number	ØD1	ØD2	L1	L2	L3	SW	$T_A$	$M$	$F_A$	$P_w$	$P_n$	Weight (g)	Price each	
							max. (Nm)	max. (Nm)	max. (kN)	max. (N/mm <sup>2</sup> )	max. (N/mm <sup>2</sup> )			
SUP-006/CC/SS	6	12	19	15	9	14	7	8,5	2,8	154	119	17	-	84,35 €
SUP-008/CC/SS	8	14	22	17	11	16	12	16,4	4,1	125	121	23	-	87,21 €
SUP-010/CC/SS	10	18	24	19	12	22	24	34,0	6,8	155	127	46	-	94,44 €
SUP-012/CC/SS	12	20	24	19	12	22	31	45,7	7,6	144	128	45	-	95,03 €
SUP-016/CC/SS	16	24	28	22	15	27	46	74,2	9,3	109	107	70	-	105,62 €
SUP-020/CC/SS	20	30	36	27	17	36	113	173,6	17,4	141	145	213	-	122,52 €
SUP-025/CC/SS	25	38	41	30	20	46	175	277,9	22,3	121	122	310	-	153,07 €
SUP-030/CC/SS	30	42	44	33	23	50	249	423,5	28,3	113	123	348	-	164,35 €

Dimensions in mm

# Hexagonal clamping hub



## Technical files

- Example of shaft-pinion hub installation


### Pre-centring

For longer pinions, the diagram below shows an additional support solution on the shaft.

- With this support, forces beyond the effective length of the hub can be absorbed
- Concentricity accuracy is improved.





External hex nut



External hex nut  
and hexagonal locknut


### No axial shift

If the pinion rests on a flange during assembly, this prevents axial movement. In this case, only 60% of the forces shown in the tables can be transmitted.



### Two shaft-pinion hubs in one pinion

In this arrangement, the first nut locked transmits 100% of the forces shown in the tables. Tightening the 2nd nut prevents any axial displacement of the hub. Therefore, this hub can only transmit 60% of the indicated forces.





# Hexagonal clamping hub

## Technical files

Shaft-pinion hubs with and without hexagonal locknuts allow the rational assembly of all types of shaft-pinion installation of machine elements such as sprockets, gear wheels, pulleys, cams, levers, etc..



### Installation

- ① The contact surfaces on the shaft and pinion must be free from oil and dust.
- ② Screw the nut on the left until the inner part protrudes approx. 3-5mm beyond the outer part.
- ③ Install the shaft-pinion hub with a mallet into the hole.
- ④ Slightly tighten the nut in the desired position. Compensate for the axial displacement caused with a soft face mallet and screw the nut on tightly.

### Removal

- Loosen the shaft-pinion hub by turning the hex nut to the left, until the inner part protrudes from the outer part by approx. 3-5mm.  
When installed in a blind hole, the shaft-pinion hub can be removed with an extraction tool.

### Example of assembly



stainless  
steel



Clamping hub  
(cat. 2 p.125)



Clamping hub  
(cat. 2 p.124)



Clamping hub  
(cat. 2 p.127)



Clamping hub  
(cat. 2 p.126)

# Installation tools

New

## SUPtool For hexagonal clamping hub

- Open-ended wrench for installation  
steel and stainless steel clamping hubs SUP

### Accessory

- SUP clamping hub (cat. 2 p.124)

NEW!



### DISCOUNTS

Qty	1+	2+	5+
Disc. Prix	-5%	-5%	On request

Part number	SW	Weight (g)	Unit Price
SUP-14/TOOL	14	45	7,09 €
SUP-16/TOOL	16	51	9,62 €
SUP-22/TOOL	22	195	16,53 €
SUP-27/TOOL	27	195	27,09 €
SUP-36/TOOL	36	428	43,52 €
SUP-46/TOOL	46	612	95,03 €
SUP-50/TOOL	50	870	101,66 €
SUP-55/TOOL	55	1125	113,31 €
SUP-65/TOOL	65	1295	114,70 €

Dimensions in mm

## Our other products



PLN

Cylindrical spacer,  
Thermoplastic



AT5M AT10M

AT type timing belt  
per metre, AT10 Steel  
cored polyurethane



WW20

Drylin® W slide, slide  
assembly



SHW

Plain washer, A2  
Stainless steel



MBF

Threaded blocking  
clamp, Threaded  
locking clamp



FBL4004\_K7

Brush strip per meter  
PA6 fibres Ø0.3 to  
Ø0.5, Black polyamide  
6 -...



NTMdI

Set screw delrin tip,  
Delrin-point




ZG0

Plastic spur gear,  
Machined plastic  
(delrin)




CLB\_T

Die cast zinc clamping  
lever - male, Zamak



RPP5

RPP heavy duty  
timing belt, RPP5



PF20NM

Worm and wheel gear  
reducer, up to 5 Nm



WINGbr

Wing screw, hand  
tightened DIN316,  
Brass DIN 316

## Complementary products



SUP

Self-centering  
clamping hub steel,  
Without locknut



SUPCC

Self-centering  
clamping hub steel,  
With lock nut



SUPccss

Self-centering  
clamping hub  
stainless steel, With  
lock nut



SUPTOOL

Installation tools for  
clamping hub, For  
hexagonal clamping  
hub