

Self-centering clamping hub steel

SUP

Without locknut

- Hexagonal clamping hub
- Effective for all types of shaft-pinion assemblies such as sprocket wheels, gear wheels, pulleys, cams etc..
- Materials:
 - External part: galvanised steel
 - Internal part: nickel-plated steel
 - Nut: nickel-plated steel

NEW!




Reduced installation time

Benefits

- Self-centering
- Reduced installation time

Info

- T_A : Tightening torque of the nut
- M : Transferable torque
- F_A : Transmissible axial load
- P_W : Surface pressure of the shaft
- P_N : Hub surface pressure



Accessory

- Assembly tool SUP/TOOL (cat. 2 p.130)

DISCOUNTS

Qty	1+	6+	10+
Disc.	Price	-5%	On request

Part number	ØD1	ØD2	L1	L2	SW	T_A max. (Nm)	M max. (Nm)	F_A max. (kN)	P_W max. (N/mm ²)	P_N max. (N/mm ²)	Weight (g)	Stock*	Price each 1 to 5
SUP-005	5	14	19	15	14	9,9	10,1	4,0	264	96	20	✓	29,66 €
SUP-006	6	14	19	15	14	9,9	12,1	4,0	220	96	19	✓	29,66 €
SUP-008	8	16	22	17	16	16,9	23,4	5,8	179	91	26	✓	30,86 €
SUP-009	9	20	24	19	22	34,9	43,7	9,7	245	115	47	-	32,04 €
SUP-010	10	20	24	19	22	34,9	48,6	9,7	221	115	46	✓	32,82 €
SUP-011	11	22	24	19	22	43,8	59,9	10,9	225	117	51	-	34,81 €
SUP-012	12	22	24	19	22	43,8	65,3	10,9	206	117	49	✓	35,60 €
SUP-014	14	26	28	22	27	65,0	93,0	13,3	178	99	83	✓	38,75 €
SUP-015	15	26	28	22	27	65,0	99,0	13,3	166	99	75	✓	38,75 €
SUP-016	16	26	28	22	27	65,0	106,0	13,3	156	99	73	✓	38,75 €
SUP-018	18	35	36	27	36	161,0	223,0	24,8	224	125	201	-	42,31 €
SUP-019	19	35	36	27	36	161,0	235,0	24,8	212	125	189	-	41,25 €
SUP-020	20	35	36	27	36	161,0	248,0	24,8	201	125	186	✓	42,31 €
SUP-022	22	42	41	30	46	250,0	349,0	31,8	197	110	346	✓	46,57 €
SUP-024	24	42	41	30	46	250,0	381,0	31,8	180	110	326	-	46,57 €
SUP-025	25	42	41	30	46	250,0	397,0	31,8	173	110	315	✓	46,57 €
SUP-028	28	47	44	33	50	355,0	565,0	40,4	174	110	403	-	53,51 €
SUP-030	30	47	44	33	50	355,0	605,0	40,4	162	110	378	✓	54,77 €
SUP-032	32	55	51	38	55	490,0	764,0	47,8	166	102	632	-	65,16 €
SUP-035	35	55	51	38	55	490,0	836,0	47,8	151	102	571	✓	65,16 €
SUP-038	38	62	58	43	65	720,0	1179,0	62,1	159	111	897	-	84,94 €
SUP-040	40	62	58	43	65	720,0	1241,0	62,1	151	111	842	-	84,94 €

Dimensions in mm

- Hexagonal clamping hub
- Effective for all types of shaft-pinion assemblies such as sprocket wheels, gear wheels, pulleys, cams etc..
- Materials:
 - External part: galvanised steel
 - Internal part: nickel-plated steel
 - Nut: nickel-plated steel

Benefits

- Self-centering
- Reduced installation time
- The hexagonal locknut makes it easier to lock the shaft-pinion assembly if freely rotating shafts.


Info

- T_A : Tightening torque of the nut
- M : Transferable torque
- F_A : Transmissible axial load
- P_W : Surface pressure of the shaft
- P_N : Hub surface pressure


Accessory

- Assembly tool SUP/TOOL (cat. 2 p.130)

NEW!



Easier locking



DISCOUNTS

Qty	1+	6+	10+
Disc.	Price	-5%	On request

Part number	ØD1	ØD2	L1	L2	L3	SW	T_A max.	M max.	F_A max.	P_W max.	P_N max.	Weight (g)	Price each
							(Nm)	(Nm)	(kN)	(N/mm ²)	(N/mm ²)		1 to 5
SUP-005/CC	5	12	19	15	9	14	9,9	10,1	4,0	264	119	18	- 35,11 €
SUP-006/CC	6	12	19	15	9	14	9,9	12,1	4,0	220	119	17	- 33,83 €
SUP-008/CC	8	14	22	17	11	16	16,9	23,4	5,8	179	121	23	- 35,60 €
SUP-009/CC	9	18	24	19	12	22	34,9	43,7	9,7	245	127	47	- 36,88 €
SUP-010/CC	10	18	24	19	12	22	34,9	48,6	9,7	221	127	46	- 37,87 €
SUP-011/CC	11	20	24	19	12	22	43,8	59,9	10,9	225	128	47	- 40,24 €
SUP-012/CC	12	20	24	19	12	22	43,8	65,3	10,9	206	128	45	- 41,25 €
SUP-014/CC	14	24	28	22	15	27	65,0	93,0	13,3	178	107	78	- 45,49 €
SUP-015/CC	15	24	28	22	15	27	65,0	99,0	13,3	166	107	75	- 45,49 €
SUP-016/CC	16	24	28	22	15	27	65,0	106,0	13,3	156	107	70	- 45,49 €
SUP-018/CC	18	30	36	27	17	36	161,0	223,0	24,8	224	145	179	- 50,83 €
SUP-019/CC	19	30	36	27	17	36	161,0	235,0	24,8	212	145	169	- 49,44 €
SUP-020/CC	20	30	36	27	17	36	161,0	248,0	24,8	201	145	213	- 50,83 €
SUP-022/CC	22	38	41	30	20	46	250,0	349,0	31,8	197	122	341	- 57,36 €
SUP-024/CC	24	38	41	30	20	46	250,0	381,0	31,8	180	122	320	- 57,36 €
SUP-025/CC	25	38	41	30	20	46	250,0	397,0	31,8	173	122	310	- 57,36 €
SUP-028/CC	28	42	44	33	23	50	355,0	565,0	40,4	174	123	370	- 63,60 €
SUP-030/CC	30	42	44	33	23	50	355,0	605,0	40,4	162	123	348	- 65,16 €
SUP-032/CC	32	50	51	38	28	55	490,0	764,0	47,8	166	112	555	- 77,24 €
SUP-035/CC	35	50	51	38	28	55	490,0	836,0	47,8	151	112	501	- 77,24 €

Dimensions in mm

Self-centering clamping hub stainless steel Sta

SUP_{SS}

Without locknut

- Hexagonal clamping hub

- Effective for all types of shaft-pinion assemblies such as sprocket wheels, gear wheels, pulleys, cams etc..

- Materials

External part: nickel-plated stainless steel

Internal part: nickel-plated stainless steel

Nut: stainless steel, hardened and nickel-plated

Benefits

- Self-centering
- Reduced installation time

Info

- T_A : Tightening torque of the nut
- M : Transferable torque
- F_A : Transmissible axial load
- P_W : Surface pressure of the shaft
- P_N : Hub surface pressure

Accessory



- Assembly tool SUP/TOOL (cat. 2 p.130)

NEW!



stainless steel

Reduced installation time



DISCOUNTS

Qty	1+	2+	5+
Disc.	Price	-5%	On request

Part number	ØD1	ØD2	L1	L2	SW	T_A max. (Nm)	M max. (Nm)	F_A max. (kN)	P_W max. (N/mm ²)	P_N max. (N/mm ²)	Weight (g)	Price each
SUP-006/SS	6	14	19	15	14	7	8,5	2,8	154	67	19	77,42 €
SUP-008/SS	8	16	22	17	16	12	16,4	4,1	125	64	26	77,42 €
SUP-010/SS	10	20	24	19	22	24	34,0	6,8	155	81	46	88,22 €
SUP-012/SS	12	22	24	19	22	31	45,7	7,6	144	82	49	88,12 €
SUP-016/SS	16	26	28	22	27	46	74,2	9,3	109	69	73	97,40 €
SUP-020/SS	20	35	36	27	36	113	173,6	17,4	141	88	186	114,60 €
SUP-025/SS	25	42	41	30	46	175	277,9	22,3	121	77	315	138,13 €
SUP-030/SS	30	47	44	33	50	249	423,5	28,3	113	77	378	138,03 €

Dimensions in mm

HPC

WEB
04/2021

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

NEW!

- Hexagonal clamping hub
- Effective for all types of shaft-pinion assemblies such as sprocket wheels, gear wheels, pulleys, cams etc..
- Materials:
 - External part: nickel-plated stainless steel
 - Internal part: nickel-plated stainless steel
 - Nut: stainless steel, hardened and nickel-plated

Benefits


- Self-centering
- Reduced installation time
- The hexagonal locknut makes it easier to lock the shaft-pinion assembly if freely rotating shafts.

Info

- T_A : Tightening torque of the nut
- M : Transferable torque
- F_A : Transmissible axial load
- P_w : Surface pressure of the shaft
- P_N : Hub surface pressure



Accessory

- Assembly tool **SUP/TOOL** (cat. 2 p.130)



stainless steel

Easier locking



DISCOUNTS

Qty	1+	2+	5+
Disc.	Price	-5%	On request

Part number							T_A	M	F_A	P_w	P_N	Weight (g)	Price each
	ØD1	ØD2	L1	L2	L3	SW	max. (Nm)	max. (Nm)	max. (kN)	max. (N/mm ²)	max. (N/mm ²)		
SUP-006/CC/SS	6	12	19	15	9	14	7	8,5	2,8	154	119	17	- 84,35 €
SUP-008/CC/SS	8	14	22	17	11	16	12	16,4	4,1	125	121	23	- 87,21 €
SUP-010/CC/SS	10	18	24	19	12	22	24	34,0	6,8	155	127	46	- 94,44 €
SUP-012/CC/SS	12	20	24	19	12	22	31	45,7	7,6	144	128	45	- 95,03 €
SUP-016/CC/SS	16	24	28	22	15	27	46	74,2	9,3	109	107	70	- 105,62 €
SUP-020/CC/SS	20	30	36	27	17	36	113	173,6	17,4	141	145	213	- 122,52 €
SUP-025/CC/SS	25	38	41	30	20	46	175	277,9	22,3	121	122	310	- 153,07 €
SUP-030/CC/SS	30	42	44	33	23	50	249	423,5	28,3	113	123	348	- 164,35 €

Dimensions in mm

Hexagonal clamping hub



Technical files

- Example of shaft-pinion hub installation


Pre-centring

For longer pinions, the diagram below shows an additional support solution on the shaft.

- With this support, forces beyond the effective length of the hub can be absorbed
- Concentricity accuracy is improved.





External hex nut



External hex nut
and hexagonal locknut


No axial shift

If the pinion rests on a flange during assembly, this prevents axial movement. In this case, only 60% of the forces shown in the tables can be transmitted.



Two shaft-pinion hubs in one pinion

In this arrangement, the first nut locked transmits 100% of the forces shown in the tables. Tightening the 2nd nut prevents any axial displacement of the hub. Therefore, this hub can only transmit 60% of the indicated forces.





Hexagonal clamping hub

Technical files

Shaft-pinion hubs with and without hexagonal locknuts allow the rational assembly of all types of shaft-pinion installation of machine elements such as sprockets, gear wheels, pulleys, cams, levers, etc..

Installation



- ① The contact surfaces on the shaft and pinion must be free from oil and dust.
- ② Screw the nut on the left until the inner part protrudes approx. 3-5mm beyond the outer part.
- ③ Install the shaft-pinion hub with a mallet into the hole.
- ④ Slightly tighten the nut in the desired position. Compensate for the axial displacement caused with a soft face mallet and screw the nut on tightly.

Removal

- Loosen the shaft-pinion hub by turning the hex nut to the left, until the inner part protrudes from the outer part by approx. 3-5mm.

When installed in a blind hole, the shaft-pinion hub can be removed with an extraction tool.


Example of assembly



stainless
steel



Clamping hub
(cat. 2 p.125)



Clamping hub
(cat. 2 p.124)



Clamping hub
(cat. 2 p.127)



Clamping hub
(cat. 2 p.126)

SUPtool For hexagonal clamping hub

- Open-ended wrench for installation steel and stainless steel clamping hubs SUP

Accessory

- SUP clamping hub (cat. 2 p.124)

NEW!



DISCOUNTS

Qty	1+	2+	5+
Disc.	Prix -5%		On request

Part number	SW	Weight (g)	Unit Price
SUP-14/TOOL	14	45	7,09 €
SUP-16/TOOL	16	51	9,62 €
SUP-22/TOOL	22	195	16,53 €
SUP-27/TOOL	27	195	27,09 €
SUP-36/TOOL	36	428	43,52 €
SUP-46/TOOL	46	612	95,03 €
SUP-50/TOOL	50	870	101,66 €
SUP-55/TOOL	55	1125	113,31 €
SUP-65/TOOL	65	1295	114,70 €

Dimensions in mm

Our other products



SSG2_304L
Stainless steel spur gear, Stainless steel 304L



CLLCLLP
Clevis components, long version, Steel - long version



CHA_GC_9SS
Stainless steel garnet hinge, To be welded



CHM110
Worm and wheel gear reducer, up to 980 Nm



UGH50
H Type Guide units, For Ø50 actuators



BGC
Oldham coupling, Clamp



MEB
Moulded plastic bevel gear (nylon), 1:1




H2
Crossed helical gear crossed axis at 90°, Steel 20NCD2



DIA
Ring operated locking bolt, with ring



FB_ECO
Eco. range steel bevel gear, 4:1



CFC
Spring loaded position switch, Electric



GTC
Belt tensioner, For standard applications

Complementary products



SUP
Self-centering clamping hub steel, Without locknut



SUPCC
Self-centering clamping hub steel, With lock nut



SUPccss
Self-centering clamping hub stainless steel, With lock nut



SUPTOOL
Installation tools for clamping hub, For hexagonal clamping hub