

Locking castor with central hole





RIM

For loads up to 1000kg

- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C

Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate has a threaded central hole, threaded rod and nut supplied.
- Wheel: Black polyamide Shore D 70



DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	ØT	Swivel interference ØK	Load (kg)	Price each 1 to 5
RIM42-60/TCE	42	20	71	81	M8	84	60	46,66 €
RIM50-280/TCE	50	25	82	92	M12	101	280	74,11 €
RIM63-550/TCE	63	28	103	118	M12	125	550	100,71 €
RIM75-800/TCE	75	30	120	132	M16	142	800	111,33 €
RIM75-1000/TCE	75	30	120	132	M16	142	1000	132,76 €

Dimensions in mm

HPC

WEB
2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



RFK58B

Hypoid gearbox -
Stainless steel, up to
500 Nm



RBGtc

Swivel castor with
central hole, Steel -
grey rubber



SHTC

Drylin® Linear table,
Maintenance free



MEP

Revolving handle for
handwheel, Fixed



PLM-SC

Magnetic stud with
threaded hole, With
threaded hole



DOMI50

Domino 50 adjustable
slide, Slide DOMILINE
50



ABL100005

Antistatic brush,
Standard



HLC19

Right angle spiro
bevel gearbox, Up to
43Nm




LC

Friction clutch, 190 to
1800 Nm



BAGSS

Stainless steel
Clamping collar,
Stainless steel



H1

Crossed helical gear
crossed axis at 90°,
Machined plastic



STC

Shock Absorber - stop
collar, Universal
flange

Complementary products



RIMple

Locking castor, with
mounting plate



PDR-RD

Mounting feet with
integrated castors,
Offset castor