

# Rigging screw with hook/eye

Stock Ste


## TAC

## Turnbuckle

- Stamped Rigging screw with eye and hook
- Fitting component
- Material: zinc plated steel Fe430B

### Info.

- SWL: safe working load.  
The Safe Working Load is calculated by dividing the breaking load by a factor of safety of 3
- Not sold individually, please contact us for details



### DISCOUNTS

Qty	1+	5+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØM	B	C	D	E	F	G	H	L1	L2	SLW (kg)	Weight (kg)	Price each
TAC1-05	M5	80	60	40	8	62	40	6	114	176	50	0,055	2,71 €
TAC1-06	M6	80	74	47	10	76	50	8	141	200	75	0,064	3,03 €
TAC1-08	M8	105	79	52	11	88	52	10	156	236	165	0,126	3,89 €
TAC1-10	M10	125	95	61	14	114	60	11	187	276	235	0,214	5,59 €
TAC1-12	M12	140	105	65	17	122	66	16	226	311	320	0,398	8,36 €
TAC1-14	M14	170	128	85	18	147	82	15	254	378	430	0,608	11,59 €
TAC1-16	M16	190	160	97	23	172	105	20	296	466	530	0,845	16,11 €

\*Depending on availability - Dimensions in mm

HPC

WEB  
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

## Our other products



EBM

Steel U bolt, Steel



CHAPAMss

Weld-on hinge with flat end, Stainless steel or Aluminium



BCH\_SS

Mushroom headed button, M3 to M8



TB8

Cylindrical roller thrust bearing, Steel



WW10

Drylin® W slide, slide assembly



FBL6000\_K19

Brush strip per meter horsehair fibres Ø0.2, Black horsehair



AC156-157

Strike for toggle latch, 25.5mm



S20

Short housing for open linear bearing, Opened - slim



GFX

Curved tooth coupling, economy range, Steel and



PRF\_PL\_4590

Joining plate for aluminium profile, Joint plate - 45x90



EMS

Stainless steel knurled thumb nut, Knurled



ACLBMC

Detector support for aluminium profile, Sensor holder

## Complementary products



TAC\_SS

Stainless steel rigging screw (hook/eye), Stainless steel




TCC

Rigging screw (hook/hook), Steel



MDR

Dee shackle with eye bolt, Steel



CAB

Galvanised steel cable, Galvanised steel