



Closed polymer **DryLin®R** bearing

Unaffected by dirt

RJUM01
RJZM01

- Closed bearing with polymer slide surface

- Max. speed
Dry working 8m/s
With lubrication >10 m/s
- Working temperature from -60°C to +100°C
(wear increases if temperature >80°C)
- Max. load 35 N/mm²
- Recommended load 5N/mm² (linear)
- Material:
Housing: Aluminium
Bearing: DryLin®R



Fast and silent



Advantages

- Maintenance free
- Self lubricating
- 20% of weight of equivalent steel version
- Silent in operation

Accessories

- AWM aluminium shaft

Until
-22%*



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-10%	-15%	-20%	On request

Part number	Ød1	Tolerance	Ød2 (h7)	B (h10)	B1 (H10)	s (H10)	Ødn	Stock*	Price each 1 to 5
RJZM01-05	5	0,02 - 0,05	12	22	14,20	1,10	11,50	✓	14,68 €
RJZM01-08	8	0,02 - 0,05	16	25	16,20	1,10	15,20	✓	14,98 €
RJUM01-10	10	0,02 - 0,05	19	29	21,60	1,30	17,50	✓	16,13 €
RJUM01-12	12	0,02 - 0,05	22	32	22,60	1,30	20,50	✓	19,22 €
RJUM01-16	16	0,02 - 0,05	26	36	24,60	1,30	24,20	✓	21,07 €
RJUM01-20	20	0,02 - 0,06	32	45	31,20	1,60	29,60	✓	26,40 €
RJUM01-25	25	0,02 - 0,06	40	58	43,70	1,85	36,50	✓	34,02 €
RJUM01-30	30	0,02 - 0,07	47	68	51,70	1,85	43,50	✓	43,62 €
RJUM01-40	40	0,02 - 0,07	62	80	60,30	2,15	57,80	-	71,43 €
RJUM01-50	50	0,02 - 0,09	75	100	77,30	2,65	70,50	-	104,89 €

*Depending on availability - Dimensions in mm

Our other products



MDB_MTB
Moulded plastic bevel gear (nylon), 2:1




TAC_SS
Stainless steel rigging screw (hook/eye),
Stainless steel



BUH77
Motor-gearbox 12V
and 24V DC, from 0.1
to 2 Nm



BOXsap
Boxed set of spring pins ISO8752, Boxed
set - Split ISO 8752



B
Steel bevel gear, 1:1




PRF_BM
Base support plate for
aluminium profile,
Central base fixation



T5-10ECO
T type timing pulley,
Economy range - T5
aluminium



VHEH
Hexagonal headed
screw with collar
Hygienic Usit®,
Stainless steel



IN1
Internal gear,
Machined plastic
(delrin)



RPCpl
Fixed castor with
plate, Steel -
Polyamide



GP
Spring loaded toggle
latch, With padlock-
holder



BLHM60
Right angled gearbox,
double output shafts,
up to 70 Nm

Complementary products