



# Closed polymer **DryLin®R** bearing

Unaffected by dirt

RJUM01  
RJZM01

**- Closed bearing with polymer slide surface**

**- Max. speed**

Dry working 8m/s

With lubrication >10 m/s

**- Working temperature from -60°C to +100°C**

(wear increases if temperature >80°C)

**- Max. load 35 N/mm<sup>2</sup>**

**- Recommended load 5N/mm<sup>2</sup> (linear)**

**- Material:**

Housing: Aluminium

Bearing: DryLin®R



**Fast and silent**

**Advantages**

**- Maintenance free**



**- Self lubricating**

**- 20% of weight of equivalent steel version**

**- Silent in operation**

**Accessories**

**- AWM aluminium shaft**



Until  
**-22%\***

**DISCOUNTS**

Qty	1+	6+	20+	40+	60+
Disc.	List	-10%	-15%	-20%	On request

Part number	Ød1	Tolerance	Ød2 (h7)	B (h10)	B1 (H10)	s (H10)	Ødn	Stock*	Price each 1 to 5
RJZM01-05	5	0,02 - 0,05	12	22	14,20	1,10	11,50	✓	14,68 €
RJZM01-08	8	0,02 - 0,05	16	25	16,20	1,10	15,20	✓	14,98 €
RJUM01-10	10	0,02 - 0,05	19	29	21,60	1,30	17,50	✓	16,13 €
RJUM01-12	12	0,02 - 0,05	22	32	22,60	1,30	20,50	✓	19,22 €
RJUM01-16	16	0,02 - 0,05	26	36	24,60	1,30	24,20	✓	21,07 €
RJUM01-20	20	0,02 - 0,06	32	45	31,20	1,60	29,60	✓	26,40 €
RJUM01-25	25	0,02 - 0,06	40	58	43,70	1,85	36,50	✓	34,02 €
RJUM01-30	30	0,02 - 0,07	47	68	51,70	1,85	43,50	✓	43,62 €
RJUM01-40	40	0,02 - 0,07	62	80	60,30	2,15	57,80	-	71,43 €
RJUM01-50	50	0,02 - 0,09	75	100	77,30	2,65	70,50	-	104,89 €

\*Depending on availability - Dimensions in mm

## Our other products



AT10-50ECO

AT type timing pulley,  
Economy range -  
AT10 aluminium



BLOC

Doorstop, Doorstop



EHD12

Internal epicyclic  
servo reducers, from  
60 to 140 Nm



BAG

Steel Clamping collar,  
Steel




DPAK\_DKON

Progressive stop,  
Steel




RTL450

Self-centering locking  
assembly, High torque



BCM\_HPBT

Modular cylindrical  
brush, PBT polyester  
bristles



BPF

Sheet steel flanged  
bearing for light  
loads, Sheet steel



DB

Steel bevel gear, 2:1



DSF

Slip friction clutch, 4  
to 2600 Nm



DOM180

Accessories, Turntable



MEB

Moulded plastic bevel  
gear (nylon), 1:1

## Complementary products