


Self-centering locking assembly Ste ★★★

RT70

Medium/high torque

- Inserts between the shaft and the bore

- High transmissible torque
- Contact pressure spread evenly
- Easy to assembly and dismantle
- Backlash free
- No constraints due to keyway
- **Increases the resistant part of the shaft**
- Suitable for alternating rotational movements
- Materials:
Body: steel
Screws: steel DIN 912 12.9



Options

- Other diameters available (up to 180mm bore)

Info.

- * PN: hub surface pressure
- * PW: shaft surface pressure




DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØA	ØD	L1	L2	L3	L	Transmissible torque (Nm)	Pw (N/mm²)	PN (N/mm²)	Screws No.	Screws Type	Tightening torque (Nm)	Stock*	Price each 1 to 5
													✓	
RT70-19-47	19	47	26	31	39	45	350	228	98	4	M6x25	17	✓	13,43 €
RT70-20-47	20	47	26	31	39	45	390	231	100	4	M6x25	17	✓	13,43 €
RT70-22-47	22	47	26	31	39	45	440	220	95	4	M6x25	17	✓	13,43 €
RT70-24-50	24	50	26	31	39	45	519	215	102	6	M6x25	17	-	14,02 €
RT70-25-50	25	50	26	31	39	45	590	230	105	6	M6x25	17	✓	14,02 €
RT70-28-55	28	55	26	31	39	45	700	220	110	6	M6x25	17	✓	15,92 €
RT70-30-55	30	55	26	31	39	45	760	200	120	6	M6x25	17	✓	15,92 €
RT70-32-60	32	60	26	31	39	45	930	230	114	8	M6x25	17	✓	17,27 €
RT70-35-60	35	60	26	31	39	45	1030	200	119	8	M6x25	17	✓	17,27 €
RT70-38-65	38	65	26	31	39	45	1240	210	124	8	M6x25	17	✓	19,62 €
RT70-40-65	40	65	26	31	39	45	1350	200	125	8	M6x25	17	✓	19,62 €
RT70-42-75	42	75	30	36	47	55	2170	236	140	6	M8x30	41	-	26,27 €
RT70-45-75	45	75	30	36	47	55	2350	236	140	6	M8x30	41	✓	26,27 €
RT70-48-80	48	80	30	36	47	55	2510	218	135	6	M8x30	41	✓	29,36 €
RT70-50-80	50	80	30	36	47	55	2580	218	135	6	M8x30	41	✓	29,36 €
RT70-55-85	55	85	30	36	47	55	3200	223	145	8	M8x30	41	✓	33,52 €
RT70-60-90	60	90	30	36	47	55	3380	198	157	8	M8x30	41	✓	35,97 €
RT70-65-95	65	95	30	36	47	55	4160	213	140	8	M8x30	41	-	38,70 €
RT70-70-110	70	110	40	46	57	67	6840	225	143	8	M10x35	83	✓	59,06 €

*Depending on availability - Dimensions in mm

Our other products



CDRs

Retaining cable for ball pin, Retaining cable



HTD8M_20

HTD Heavy duty timing pulley, HTD8 Cast



SSDB

Stainless steel bevel gear, 2:1



PCM

Fixed cylindrical handle, Fixed non-turning handle



MLY_SS

Stainless steel bow shackle with eye bolt, Stainless steel




DKN

Bellows coupling Gerwah®, from 0.4 to 10Nm




FF30

Offset spur gear reducer, from 21.50 to 83 Nm



RPPM

RPP type belt per metre, RPP5 Steel cored polyurethane



T5M_T10M

T type timing belt per metre, T5 Steel cored




HG6

Steel spur gear, Steel 20NCD2



PO

Pull handle - Multi-sector, Tapped



MAT

Drawn ground round bar, 100C6 steel bar

Complementary products



RTL450

Self-centering locking assembly, High torque



RT25

Self-centering flanged locking assembly, Medium/high torque



RT61

Self-centering locking Assembly, Medium/low torque



RT61ss

Self-centering locking Assembly, Medium/low torque