


- Stamped Rigging screw with eye and hook
- Fitting component
- Material: zinc plated steel Fe430B



Info.

- SWL: safe working load.
The Safe Working Load is calculated by dividing the breaking load by a factor of safety of 3
- Not sold individually, please contact us for details



DISCOUNTS

| Qty | 1+ | 5+ | 10+ | 20+ | 30+ | 50+ |
|-------|------|-----|------|------|------|------------|
| Disc. | List | -5% | -10% | -15% | -20% | On request |

| Part number | ØM | B | C | D | E | F | G | H | L1 | L2 | SLW (kg) | Weight (kg) | Price each |
|-------------|-----|-----|-----|----|----|-----|-----|----|-----|-----|----------|-------------|------------|
| TAC1-05 | M5 | 80 | 60 | 40 | 8 | 62 | 40 | 6 | 114 | 176 | 50 | 0,055 | 2,59 € |
| TAC1-06 | M6 | 80 | 74 | 47 | 10 | 76 | 50 | 8 | 141 | 200 | 75 | 0,064 | 2,90 € |
| TAC1-08 | M8 | 105 | 79 | 52 | 11 | 88 | 52 | 10 | 156 | 236 | 165 | 0,126 | 3,73 € |
| TAC1-10 | M10 | 125 | 95 | 61 | 14 | 114 | 60 | 11 | 187 | 276 | 235 | 0,214 | 5,76 € |
| TAC1-12 | M12 | 140 | 105 | 65 | 17 | 122 | 66 | 16 | 226 | 311 | 320 | 0,398 | 8,01 € |
| TAC1-14 | M14 | 170 | 128 | 85 | 18 | 147 | 82 | 15 | 254 | 378 | 430 | 0,608 | 11,93 € |
| TAC1-16 | M16 | 190 | 160 | 97 | 23 | 172 | 105 | 20 | 296 | 466 | 530 | 0,845 | 16,57 € |

*Depending on availability - Dimensions in mm

Stainless steel rigging screw with hook/eye



Turnbuckle

TACss

- Rigging screw with eye and hook
- Fitting component
- Material: stainless steel 316

Info.

- SWL: safe working load.
- The Safe Working Load is calculated by dividing the breaking load by a factor of safety of 3



DISCOUNTS

| | | | | | |
|-------|------|-----|------|------|------------|
| Qty | 1+ | 5+ | 10+ | 20+ | 30+ |
| Disc. | List | -5% | -10% | -15% | On request |

| Part number | ØA | B | ØD | L1 | L2 | SWL (kg) | Weight (kg) | Stock* | Price each 1 to 4 |
|-------------|-----|------|------|-----|---------|----------|-------------|--------|-------------------|
| TAC1-05/SS | M5 | 9 | 8,3 | 71 | 122-179 | 180 | 0,046 | ✓ | 8,30 € |
| TAC1-06/SS | M6 | 9,5 | 10,0 | 90 | 160-228 | 360 | 0,076 | ✓ | 9,95 € |
| TAC1-08/SS | M8 | 11 | 12,0 | 120 | 210-303 | 650 | 0,165 | ✓ | 17,20 € |
| TAC1-10/SS | M10 | 13 | 15,8 | 150 | 255-376 | 1000 | 0,285 | ✓ | 21,96 € |
| TAC1-12/SS | M12 | 16,8 | 20,0 | 200 | 305-473 | 1400 | 0,515 | - | 33,67 € |
| TAC1-16/SS | M16 | 16,3 | 26,0 | 245 | 400-593 | 2300 | 1,110 | - | 68,29 € |

*Depending on availability - Dimensions in mm

Rigging screw with 2 hooks

Stock Ste

TCC


Turnbuckle

- Stamped Rigging screw with two hooks
- Fitting component
- Material: zinc plated steel Fe430B



Info.

- SWL: safe working load.
The Safe Working Load is calculated by dividing the breaking load by a factor of safety of 3
- ** Not sold individually, please contact us for details



DISCOUNTS

| Qty | 1+ | 5+ | 10+ | 20+ | 30+ | 50+ |
|-------|------|-----|------|------|------|------------|
| Disc. | List | -5% | -10% | -15% | -20% | On request |

| Part number | ØM | B | C | D | E | L1 | L2 | SWL (kg) | Weight (kg) | Stock* | Price each 1 to 4 |
|-------------|-----|-----|-----|-----|----|-----|-----|----------|-------------|--------|-------------------|
| TCC1-05 | M5 | 80 | 62 | 40 | 6 | 116 | 178 | 50 | 0,052 | ✓ | 2,69 € |
| TCC1-06 | M6 | 80 | 76 | 50 | 8 | 143 | 205 | 75 | 0,065 | ✓ | 2,98 € |
| TCC1-08 | M8 | 105 | 88 | 52 | 10 | 165 | 245 | 165 | 0,136 | ✓ | 4,06 € |
| TCC1-10 | M10 | 125 | 111 | 60 | 12 | 213 | 307 | 235 | 0,220 | ✓ | 6,20 € |
| TCC1-12 | M12 | 140 | 130 | 66 | 15 | 252 | 350 | 320 | 0,420 | - | 8,12 € |
| TCC1-14 | M14 | 170 | 147 | 86 | 15 | 277 | 407 | 420 | 0,640 | - | 13,28 € |
| TCC1-16 | M16 | 190 | 172 | 105 | 20 | 298 | 463 | 530 | 0,880 | - | 17,63 € |

*Depending on availability - Dimensions in mm

Stainless steel rigging screw with 2 hooks



Turnbuckle

TCCss

- Rigging screw with two hooks
- Fitting component
- Material:
Clamp : stainless steel 316

Info.

- SWL: safe working load.
The Safe Working Load is calculated by dividing the breaking load by a factor of safety of 3



DISCOUNTS

| | | | | | |
|-------|------|-----|------|------|------------|
| Qty | 1+ | 5+ | 10+ | 20+ | 30+ |
| Disc. | List | -5% | -10% | -15% | On request |

| Part number | ØA | B | L1 | L2 | SWL (kg) | Weight (kg) | Stock* | Price each 1 to 4 |
|-------------|-----|----|-----|---------|----------|-------------|--------|-------------------|
| TCC1-05/SS | M5 | 9 | 71 | 128-184 | 180 | 0,045 | ✓ | 8,30 € |
| TCC1-06/SS | M6 | 10 | 90 | 160-228 | 360 | 0,075 | ✓ | 9,95 € |
| TCC1-08/SS | M8 | 9 | 120 | 215-309 | 650 | 0,165 | - | 17,20 € |
| TCC1-10/SS | M10 | 12 | 150 | 265-380 | 1000 | 0,280 | - | 21,96 € |
| TCC1-12/SS | M12 | 15 | 200 | 310-480 | 1400 | 0,510 | - | 33,67 € |
| TCC1-16/SS | M16 | 16 | 243 | 400-594 | 2300 | 1,060 | - | 68,29 € |

*Depending on availability - Dimensions in mm