

Fixed castor for aluminium profile

TPEF

For loads up to 120kg

- Castor for aluminium profil 40/45mm such as PRF4545

- Materials:

Plate: powder-coated steel sheet, natural aluminium colour

Wheel: grey polypropylene (RAL 7001)

Advantages


- Silent
- Will not mark floor
- Low rolling resistance

Info

- Fixing screws not supplied (See PRF-ECL-M8 (tome 5 p.315) and BHC8 (tome 1 p.562) CHC8-SS (tome 1 p.559) screws)



Typical application



Does not protrude from the profile after assembly

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	H	Maximum load (N)	Weight (g)	Price each 1 to 9
TPE80/F	80	111	1000	484	27,88 €
TPE100/F	100	136	1100	577	33,49 €
TPE125/F	125	161	1200	675	37,52 €

Dimensions in mm

Swivel castor for aluminium profile

For loads up to 120kg

TPEPDB

- Swivel castor with brake for use with aluminium profile 40/45mm such as PRF4545
- Material:
 - Plate: powder-coated steel sheet, natural aluminium colour
 - Wheel: grey polypropylene (RAL 7001)

Advantages

- Silent
- Will not mark floor
- Low rolling resistance


Info

- Fixing screws not supplied
- See PRF-ECL-M8 (tome 5 p.315) and BHC8 (tome 1 p.562) CHC8-SS (tome 1 p.559) screws



Typical application

Does not protrude from the profile after assembly



REMISES

Qté	1+	10+	30+
Rem.	Prix	-5%	Sur demande

Part number	ØD	H	Maximum load (N)	Weight (g)	Price each 1 to 9
TPE80/PDB	80	111	1000	710	41,31 €
TPE100/PDB	100	136	1100	787	45,10 €
TPE125/PDB	125	161	1200	873	50,49 €

Dimensions in mm

Retractable castor for aluminum profile

RESC

Load up to 200kg

- Retractable castor with foot, allowing easy transition from a rolling position to a fixed position.

- Materials:

Black PU tread

Wheel centre PA grey sim. RAL7001

Die-cast aluminium base plate



Steel wheel support

Advantages

- Allows the wheel to be shifted effortlessly into a fixed position thanks to the lever arm.
- Standing position more stable than a caster with brake.
- Prevents deformation of the tread under prolonged load.
- Can be mounted with the aluminium section in several different combinations.

Accessories

- Compatible with sections that have a width of 45mm PRF4545 and 90mm PRF4590 (tome 5 p.299)
- Compatible with section widths measuring 40mm, 80mm and 90mm
- CHC8-40/SS/B screw (tome 1 p.559)
- PRF-ECL-M8 nut (tome 5 p.315)



Application examples

DISCOUNTS

Qty	1+	10+	30+
Disc.	Price	-5%	On request

Part number	ØD	E	H	L1	L2	Max load (N)	Weight (kg)	Price per unit 1 to 9
RESC80-125	80	25.3	125	117	153	1500	1.64	192,56 €
RESC100-145	100	25.3	145	117	153	2000	1.94	195,13 €

Dimensions in mm