

Fixed castor for aluminium profile

TPEF

For loads up to 120kg

- Castor for aluminium profil 40/45mm
such as PRF4545

- Materials:

Plate: powder-coated steel sheet,
natural aluminium colour

Wheel: grey polypropylene (RAL 7001)

Advantages


- Silent
- Will not mark floor
- Low rolling resistance

Info

- Fixing screws not supplied
(See PRF-ECL-M8 and BHC8/CHC8 screws)



Typical application



DISCOUNTS

| Qty | 1+ | 10+ | 30+ |
|-------|------|-----|------------|
| Disc. | List | -5% | On request |

| Part number | ØD | H | Maximum load (N) | Weight (g) | Price each 1 to 9 |
|-------------|-----|-----|------------------|------------|-------------------|
| TPE80/F | 80 | 111 | 1000 | 484 | 22.58 € |
| TPE100/F | 100 | 136 | 1100 | 577 | 27.13 € |
| TPE125/F | 125 | 161 | 1200 | 675 | 30.39 € |

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com


Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



SBF

Sealed flange bearing unit for Food Industry, cover



AWMP

Aluminium shaft for linear guide, Aluminium



PW_PWG2

Worm - precision range, Steel




DP

Dowel pin, Solid ISO 2338



MAC

Carabiner DIN5299 steel, Steel



TSM T10M

T type timing belt per metre, T10 Steel cored polyurethane



MDB_MTB

Moulded plastic bevel gear (nylon), 3:1



CHM30-MOT

Asynchronous AC motorgearboxes 0.09 to 0.22kW, 0.09 to 0.22kW



BTCW

Cap for square tube to be welded, To be



LVT

Miniature motorised actuator 2A, 2 amperes



CABPVC

PVC covered galvanised steel



RCX-6

Spherical tilt washer - DIN6319, concave

Complementary products

transparen...



TPEpbd

Castor for aluminium profile, Swivel with brake



PRF4545

Standard aluminium profile, 45 x 45 mm



PRF_ECL

Nut for aluminium profile, Steel square nut with tab



BHC

Socket head button screw, Stainless steel A2