


SZZ

With protective shields

- Radial contact ball bearings
- Single row of balls
- With 2 protective shields (ZZ joints)
- Tolerance: P6/ABEC3
- Material: stainless steel AISI 440C
- Static and dynamic loads : these bearings can handle approx 70% of the same loads that an equivalent steel bearing will accept
- Max. working temperature: +80°C



stainless steel



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-10%	-15%	-20%	On request


Part number	ØA	ØD	E	Dynamic load (N)	Static load (N)	Stock*	Price each 1 to 5
S682ZZ	2	5	2,3	137,29	39,23	✓	23,04 €
S683ZZ	3	7	3,0	254,97	78,45	✓	17,23 €
S684ZZ	4	9	4,0	509,95	176,52	✓	17,23 €
S685ZZ	5	11	5,0	598,21	225,55	✓	16,30 €
S686ZZ	6	13	5,0	853,18	343,23	✓	16,30 €
S687ZZ	7	14	5,0	961,05	402,07	✓	17,30 €
S688ZZ	8	16	5,0	1029,70	460,91	✓	19,88 €
S608ZZ	8	22	7,0	2726,25	1068,92	✓	35,35 €
S689ZZ	9	17	6,0	1098,34	529,56	-	21,17 €
S6800ZZ	10	19	5,0	1441,58	657,05	✓	38,63 €
S6801ZZ	12	21	5,0	1569,06	853,18	✓	52,95 €
S6802ZZ	15	24	5,0	2029,98	1225,83	✓	67,11 €
S6803ZZ	17	26	5,0	1824,04	1196,41	-	73,48 €
S6804ZZ	20	32	7,0	3314,65	2029,98	✓	87,13 €

*Depending on availability - Dimensions in mm

Our other products



RFV40
Stainless steel worm and wheel gearbox, up to 47 Nm



H1
Crossed helical gear crossed axis at 90°, Machined plastic (delrin)



BHC
Socket head button screw, Stainless steel A2



MDPOT
Potentiometer,



DOMI50
Accessories, Fixing kit



D-PAR_SS
Stainless steel elastomeric mount, stainless steel



CHAR16Q46
Spring hinge, screwed



CLLCLLP
Clevis components, long version, Steel - long range



BSM
Spring plunger with internal hexagonal socket, steel body,



PW_PWG15
Worm - precision range, Steel



PT881
Drive sprocket for slat top chain, Range 881



BLHB30
Right angled gearbox, bored shafts, up to 4.4 Nm

Complementary products



SF_ZZ
Deep groove ball bearing, Stainless steel



S_2RS
Deep groove ball bearing, Stainless steel



FUSS
Bearing locknut, Self locking locknut - stainless steel lock washer