

Fixed castor for aluminium profile

TPEF

For loads up to 120kg

- Castor for aluminium profil 40/45mm
such as PRF4545

- Materials:

Plate: powder-coated steel sheet,
natural aluminium colour

Wheel: grey polypropylene (RAL 7001)

Advantages


- Silent
- Will not mark floor
- Low rolling resistance

Info

- Fixing screws not supplied
(See PRF-ECL-M8 and BHC8/CHC8 screws)



Typical application



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	H	Maximum load (N)	Weight (g)	Price each 1 to 9
TPE80/F	80	111	1000	484	22.58 €
TPE100/F	100	136	1100	577	27.13 €
TPE125/F	125	161	1200	675	30.39 €

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



PLC_PLT

Magnetic stud with threaded hole, With threaded hole



PRF19_E

Bracket for aluminium profile, PRF19 to PRF45




ADL_F

Female eye bolt conforms to DIN582, Steel



BOX-NINA

Self locking nut - DIN985, Box set of steel nuts



PF45

Worm and wheel gear reducer, up to 40 Nm



AT5courroie

AT type timing belt, AT5 Steel cored polyurethane



LRR

Spring loaded latch, Spring loaded latch



DOMI30

Accessories, Fixing kit



GPBSS

Threaded spherical knob, Stainless steel




GB-RA

Brass spur gear, Brass CuZn39Pb3



GAL_25

Ø25 conveyor roller, Without ball bearing



SHWbr

Washer - DIN125, Brass

Complementary products



TPEpbd

Castor for aluminium profile, Swivel with brake



PRF4545

Standard aluminium profile, 45 x 45 mm



PRF_ECL_

Nut for aluminium profile, Steel square nut with tab



BHC

Socket head button screw, Stainless steel A2