

- Closed housing
- SA: Housing only
- SAKH : Housing and light KH bearing with seal
- Material: anodised aluminium

Accessories



- Hardened ground shafts Z-A, Z-B
- End support for shafts FGWA, SFWR



SA: housing only



SAKH: housing + KH bearing



DISCOUNTS

Qty	1+	5+	10+	25+
Disc. List	-6%	-12%	On request	

Part number	Housing only	Housing and bearing	For shaft Ød	ØD	A	C	H	A1 +/-0,15	C1
SA12	SAKH-12-LL		12	19	40	28	33	29	14
SA16	SAKH-16-LL		16	24	45	30	38	34	15
SA20	SAKH-20-LL		20	28	53	30	45	40	15
SA25	SAKH-25-LL		25	35	62	40	54	48	20
SA30	SAKH-30-LL		30	40	67	50	60	53	25
SA40	SAKH-40-LL		40	52	87	60	76	69	30
SA50	SAKH-50-LL		50	62	103	70	92	82	35

Part number	Housing only	Housing and bearing	H1 +0,010 -0,02	H2	H3	ØM	Ød1	Stock* Housing + bearing	Price each 1 to 4 Housing only	Housing + bearing
SA12	SAKH-12-LL		17	11	16	M5	4,3	✓	35,07 €	49,79 €
SA16	SAKH-16-LL		19	11	18	M5	4,3	✓	36,65 €	55,56 €
SA20	SAKH-20-LL		23	13	22	M6	5,3	✓	40,85 €	61,84 €
SA25	SAKH-25-LL		27	18	26	M8	6,6	✓	51,37 €	74,43 €
SA30	SAKH-30-LL		30	18	29	M8	6,6	✓	67,07 €	98,58 €
SA40	SAKH-40-LL		39	22	38	M10	8,4	-	99,62 €	145,79 €
SA50	SAKH-50-LL		47	26	46	M12	10,5	-	131,12 €	188,83 €

*Depending on availability - Dimensions in mm

Our other products



PRF-SCL

Lock for aluminium profile, Lock for sliding doors



MSP3815

Masterplate® glueable insert rectangular, rectangular with



UCFL-PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



AC144

Strike for toggle latch, 22mm



GLB

Small 6 lobe threaded handle - female, Technopolymer - Brass



PCS50K

Chain sprocket with hardened teeth, 12.7mm (DIN08B-1)




BEAS

Knob star grip antistatic, Star, anti-static



PW_PWG1

Worm - precision range, Steel



AC

Strike for toggle latch, 15mm



KB_OP

Open precision linear bearing, Precision -



SLB

Indexing plunger, steel class 5.8



BAG

Steel Clamping collar, Steel

Complementary products



ZA

Shaft for linear guides, Hardened ground steel



FGWA

End support, With base



ZA

Shaft for linear guides, Hardened ground steel