


Suction cup threaded insert


Socket screw

SCR
ADAG

- Material: nickel brass




Assembly diagram




Socket screw insert



Adaptor



female



male

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc. List	-5%	-10%	-15%	On request	

Insert socket head

Part number	Ø	H	For suction cup	For adaptor	Stock*	Price each 1 to 49
SCR15M5	M5	9	DFG15	ADAG18M5F	✓	2,21 €
SCR20M5	M5	11	DFG20	ADAG18F5F	✓	3,28 €
SCR30M6	M6	19	DCA33, DCA43, DCG30, DCG40, DCG60	ADAG18F6F, ADAG18M6F	✓	1,85 €
SCR20BM6	M6	14	DFG25, DFG30, DFG40	ADAG14F6F	✓	3,28 €
SCR50M6	M6	17	DFG50	ADAG14M6F	✓	4,59 €

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc. List	-5%	-10%	-15%	On request	

Adaptor

Part number	ØM	H	A/F	For socket screw insert	Stock*	Price each 1 to 49
ADAG18F6F	1/8»	14,0	13	female	-	2,21 €
ADAG14F6F	1/4»	17,5	17	female	-	2,89 €
ADAG18M6F	1/8»	13,0	13	male	✓	2,21 €
ADAG14M6F	1/4»	15,0	17	male	✓	2,21 €
ADAG18M5F	1/8»	13,0	13	male	✓	2,89 €
ADAG18F5F	1/8»	14,0	13	female	-	3,13 €

*Depending on availability - Dimensions in mm

Our other products



PRF_BP
Doorstop for
aluminium profile,
Swing door stop



VAP
Magnetic stud with
central hole, With
central hole



M0
Worm and wheel set,
Bronze



PLB
Cylindrical spacer,
Brass



PSG25
Spur gear - precision
range, Pre-hardened
Steel 35NCD6




RTT
Locking Assembly,
Medium/high torque



CHINV2
Invisible hinge,
Invisible - Opening up
to 125°



HSE-HSB
Hexagonal spacer,
Brass




RPPM
RPP type belt per
metre, RPP8 Steel
cored polyurethane



PSG125HC
Skive hobbed spur
gears - precision
range, Case hardened



NCT
Square tube
connector, Fixed
angle



EZYSS
Stainless steel
cylindrical stop,
stainless steel

Complementary products



SCR
Suction cup threaded
insert, Adaptator for
insert



DCG
Suction cup, 2.5
bellows, nitrile