


H Type guide units



UGH40

For **Ø32** actuators
ISO 15552 (VDMA 24562)


- Guide system for standard pneumatic actuators
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling supplied
- Fixing holes conform to CNOMO standards
- Supplied with 4 fixing screws for actuator
- Maintenance free
- Working temperature: +5°C to +80°C
- Maximum speed: 1 m/s
- Maximum loads : See end of section



Accurate even for long strokes

Material

- Body + face plate: anodised aluminium
- Couplings + screws: Zinc plated steel
- Guide shafts: Chromed steel



Attach cylinder using 4 off M6 screws on $\varnothing 38$

DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke (mm)	Actuator Ø (mm)	Guide rod Ø (mm)	Weight (kg)	Price each
UGH40-25	25	40	16	2,38	263,22 €
UGH40-50	50	40	16	2,46	264,90 €
UGH40-100	100	40	16	2,61	268,29 €
UGH40-160	160	40	16	2,80	272,39 €
UGH40-200	200	40	16	2,92	275,06 €
UGH40-250	250	40	16	3,08	278,48 €
UGH40-320	320	40	16	3,29	283,19 €
UGH40-400	400	40	16	3,54	288,61 €
UGH40-500	500	40	16	3,85	295,39 €
UGH40-600	600	40	16	4,16	302,21 €

Dimensions in mm

Our other products



BZY_SS

Stainless steel cylindrical elastomer mount, Stainless steel



WSRM

Cylindrical polymer nut, Polymer (Iglidur®) - 1 thread



UGPL

Actuator guide kit, Long bearing



PSPE22

Conical flexible shaft handle Ø22, Black PVC




BSM

Spring plunger with internal hexagonal socket, steel body and pin



RVM25

Manually operated gearbox, Bevel



TIFbout

Threaded stud - DIN976A, Steel



VTA

Vari-Tork® slip friction clutch, 0.53 to 1.32 Nm



M1

Worm and wheel set, Non hardened steel



PGM52-M4

Pull handle, Brass



SH2

Parallel axis helical gear, Machined plastic (delrin)



ACLLPP

Latch for aluminium profile, Spring operated latch

Complementary products