

- Female threaded rod end
- Axial static load = 0.2 x radial static load

Materials:

Housing: stainless steel 303

Insert: stainless steel 303

Sphere: stainless steel 420


Coating: UNIFLON® between ring and sphere

Advantages

- Long life expectancy
- Low friction
- No maintenance required
- Corrosion resistant

Uses

- Oscillating movement in hostile environments (water, salt, dampness, other difficult atmospheric conditions...)



Swiss precision



stainless steel

DISCOUNTS

Qty	1+	10+	24+
Disc.	List	-20%	On request

Part number	ØA	B	ØD	F	G	H	ØJ	K	L	M	O	W	X
SFE3.45	3	10	12	21	27	4,50	5,00	6,50	3,00	M3 x 0,50	5,18	6	5,50
SFE5.45	5	14	16	27	35	6,00	7,50	9,50	4,00	M5 x 0,80	7,71	8	8,00
SFE6.45	6	14	18	30	39	6,75	9,50	12,00	5,00	M6 x 1	8,98	9	10,00
SFE8.45	8	17	22	36	47	9,00	12,50	16,00	5,00	M8 x 1,25	10,40	12	13,00
SFE10.45	10	20	26	43	56	10,50	15,00	19,00	6,50	M10 x 1,50	12,92	14	16,00
SFE12.45	12	22	30	50	65	12,00	17,50	22,00	6,50	M12 x 1,75	15,43	16	18,00
SFE14.45	14	27	34	57	74	13,50	20,00	25,00	8,00	M14 x 2	16,86	19	21,00
SFE16.45	16	33	38	64	83	15,00	22,00	27,00	8,00	M16 x 2	19,39	21	24,00
SFE18.45	18	36	42	71	92	16,50	25,00	31,00	10,00	M18 x 1,50	21,89	23	27,00

Part number	Radial static load (daN)	Sphere ØE	Weight (g)	Price each 1 to 5
SFE3.45	160	6,00	7	198,57 €
SFE5.45	250	11,11	14	129,44 €
SFE6.45	300	12,70	22	115,16 €
SFE8.45	450	15,88	38	122,53 €
SFE10.45	600	19,05	70	149,10 €
SFE12.45	770	22,23	110	172,26 €
SFE14.45	940	25,40	150	167,32 €
SFE16.45	1140	28,58	200	303,54 €
SFE18.45	1370	31,75	280	540,80 €

Dimensions in mm

Our other products




ACLBDB

Closing mechanism for aluminium profile, Dual ball catch



TUBE25_25

Square Tube, Aluminium or Stainless steel



PF20NM

Worm and wheel gear reducer, up to 5 Nm



PRF_GAL

Roller for aluminium profile, Flat roller



CHM63-MOT

Asynchronous AC motorgearboxes 0.37 to 1.5kW, 0.37 to 1.5kW



GE_C

Spherical bushing, Hard chromium / PTFE



VELM6

Screw-on base for hook-and-loop strip, Polyamide



PR40

Articulated foot Ø40, Ø 40



CABPVC

PVC covered galvanised steel



VTSM

Ball head screws Hygienic Design®.



CLM

Male clevis end, Stainless steel short



ERT

Sliding nut, For T slot

Complementary products

transparen...



CFF_SS

Female rod ends DIN ISO12240-4, Stainless steel / bronze - Economy r...



CFF

Female rod ends DIN ISO12240-4, Steel / bronze