


1 trapezoidal right or left-hand thread SKM SKMLH

- Right or left-hand thread
- Thread conforms to NFE 03.616
- Material: Steel 115MnPb37
- Machined nut
- Thread tolerance: 7H



Accessories

- LFM steel leadscrew or LSM stainless steel leadscrew

DISCOUNTS A

Qty	1+	10+	20+	40+
Disc.	List -30%	-40%	On request	

DISCOUNTS B

Qty	1+	5+	10+
Disc.	List -5%	On request	

Part number	Ød	Pitch P	SW	C	Weight (kg)	Stock*	Price each	
							1 to 9	40 to 59**
Right-hand thread								
SKM102	10	2	17	15	0,022	✓	A 3,37 €	A 2,02 €
SKM123	12	3	19	18	0,032	✓	A 3,80 €	A 2,27 €
SKM143	14	3	22	21	0,049	✓	A 5,21 €	A 3,13 €
SKM164	16	4	24	24	0,065	✓	A 6,54 €	A 3,92 €
SKM184	18	4	27	27	0,091	✓	A 6,95 €	A 4,17 €
SKM204	20	4	30	30	0,124	✓	A 8,02 €	A 4,81 €
SKM225	22	5	30	33	0,125	✓	A 8,72 €	A 5,23 €
SKM245	24	5	36	36	0,219	✓	A 9,98 €	A 5,99 €
SKM285	28	5	41	42	0,318	✓	A 12,79 €	A 7,67 €
SKM306	30	6	46	45	0,445	✓	A 14,88 €	A 8,93 €
SKM326	32	6	50	48	0,567	✓	A 18,22 €	A 10,93 €
SKM366	36	6	55	54	0,708	✓	B 15,93 €	B On request
SKM407	40	7	60	60	0,893	✓	B 21,05 €	B On request
SKM447	44	7	65	66	1,538	-	B 34,36 €	B On request
SKM508	50	8	75	75	1,889	✓	B 69,02 €	B On request
SKM609	60	9	90	90	3,277	-	B 98,06 €	B On request
Left-hand thread								
SKM102/LH	10	2	17	15	0,022	-	A 5,68 €	A 3,41 €
SKM123/LH	12	3	19	18	0,032	-	A 6,78 €	A 4,07 €
SKM143/LH	14	3	22	21	0,049	-	A 6,78 €	A 4,07 €
SKM164/LH	16	4	24	24	0,065	-	A 8,19 €	A 4,91 €
SKM184/LH	18	4	27	27	0,091	-	A 8,53 €	A 5,12 €
SKM204/LH	20	4	30	30	0,124	-	A 9,77 €	A 5,87 €
SKM225/LH	22	5	30	33	0,125	-	A 10,94 €	A 6,57 €
SKM245/LH	24	5	36	36	0,219	-	A 12,39 €	A 7,44 €
SKM285/LH	28	5	41	42	0,318	-	A 15,02 €	A 9,01 €
SKM306/LH	30	6	46	45	0,445	-	A 18,67 €	A 11,20 €
SKM326/LH	32	6	50	48	0,567	-	A 21,76 €	A 13,05 €
SKM366/LH	36	6	55	54	0,708	-	B 18,16 €	B On request
SKM407/LH	40	7	60	60	0,893	-	B 25,43 €	B On request
SKM447/LH	44	7	65	66	1,538	-	B 38,09 €	B On request
SKM508/LH	50	8	75	75	1,889	-	B 17,50 €	B On request
SKM609/LH	60	9	90	90	3,277	-	B 38,00 €	B On request

*Depending on availability - Dimensions in mm

** refer to discounts

Our other products



CHAE4080PA

Symmetrical decorative screwed hinge, Polyamide



BPQ

Quadro linear ball bearing unit, Included 4 linear ball bearings




PM2

Worm and wheel set, Hardened steel



ACLRP

Wheel for aluminium profile, Integrated bearing




M2

Worm and wheel set, Machined plastic (delrin)



NPTF20

Fixed tube carrier, Fixed $\varnothing 10$ to $\varnothing 14$



RPP8

RPP heavy duty timing belt, RPP8




DOMI30

Accessories, Turntable




MC

Self-compensating shock-absorber, Self-compensating -



LVTMFC

Device for controlling limit switches, For mini-actuator LVT



CF

Cam follower, Standard - steel



DTR


Chain idler sprocket, Chain idler sprocket - Steel

Complementary products



LFM

Steel leadscrew, Medium carbon steel - 1 thread




LSM

Stainless steel 316L leadscrew, Stainless steel - 1 thread



LFM

Steel leadscrew, Medium carbon steel - 1 thread



LSM

Stainless steel 316L leadscrew, Stainless steel - 1 thread