



V shaped channel UtiliTrak®

Aluminium




UTKPWRR

- For use with UTK-PWCR roller carriages
- V shaped channel made from aluminium 6063-T6
- Lightweight
- Length may vary +/- 2mm

Option

- Max rail length : 3600mm



DISCOUNTS

Qty	1+	2+	4+
Disc. List	-10%		On request

Part number	H	J	K	L	M	Dia x depth (counterbore)	T (Ø hole)	P	Rail weight (kg/m)	Carriage weight (g)	Price each
UTK0-PWRR	11,0	4,0	20	1000	20	8,3 x 3	4,8	80	0,29	47	100,71 €
UTK1-PWRR	15,0	4,0	26	1000	20	9,8 x 2,8	5,8	80	0,43	94	109,79 €
UTK2-PWRR	19,7	4,5	40	1000	20	14,3 x 3	8,8	80	0,80	246	160,32 €

Dimensions in mm

Our other products



BEAS

Star shaped anti-static handle, Star, anti-static



HG6

Steel spur gear, Steel 20NCD2



CHB

Worm and wheel gear reducer, up to 73 Nm



GET-AL

Jaw coupling, economy range, Aluminium



GLB

Small 6 lobe threaded handle - female, Technopolymer - Stainless steel



CHINV

Invisible hinge, Invisible - 90° opening



RAGFLOWsupport

Floway2® Roller track accessory, Roller track support




S_ZZ

Deep groove ball bearing, Stainless steel



CLG1

Moulded plastic spur gear, Moulded plastic (nylon)



RPP8

RPP heavy duty timing belt, RPP8



HLUMss

Revolving handle for handwheel, Stainless steel 316



J51

Spur gear coaxial gearbox, from 0.13 to 0.49 Nm - In-line

Complementary products



UTKpwcr

Utilitak® 3 wheels carriage, Polymer roller carriage



UTKpwr

Utilitak® V rail, V rail



UTKpwcr

Utilitak® 3 wheels carriage, Polymer roller carriage