



# V shaped channel UtiliTrak®

Aluminium




UTKPWRR

- For use with UTK-PWCR roller carriages
- V shaped channel made from aluminium 6063-T6
- Lightweight
- Length may vary +/- 2mm

## Option

- Max rail length : 3600mm



## DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-10%	On request

Part number	H	J	K	L	M	Dia x depth (counterbore)	T (Ø hole)	P	Rail weight (kg/m)	Carriage weight (g)	Price each
UTK0-PWRR	11,0	4,0	20	1000	20	8,3 x 3	4,8	80	0,29	47	100,71 €
UTK1-PWRR	15,0	4,0	26	1000	20	9,8 x 2,8	5,8	80	0,43	94	109,79 €
UTK2-PWRR	19,7	4,5	40	1000	20	14,3 x 3	8,8	80	0,80	246	160,32 €

Dimensions in mm

Fax: 0 825 88 6000 Service 0,15€/mln + prix appel

cial2@hpeurope.com

WEB  
04/2020

HPC

## Our other products



BPH  
Ball transfer unit plain fit, High



CFF  
Female rod ends DIN ISO12240-4, Steel / bronze



GLT3E-50  
Telescopic drawer,



PCF2  
Conical flexible mount, Oval base plate



ES  
Support base (tripod), Plastic



D19 D29  
Compression springs in metre length stainless steel, by the metre



HBM  
Adjustment bushing for half-rail guide, Adjustment bushing



RLR  
Roll-Ring® chain tensioner, Roll-Ring® Self-adjusting



SCA\_SS  
Stainless steel flat cable clamp, Stainless steel



DOMI80  
Domino 80 adjustable slide, Slide DOMILINE 80



BAGSS  
Stainless steel Clamping collar, Stainless steel



PRF\_PA  
Angle plate for aluminium profile, Adjustable plate

## Complementary products



UTKpwcr  
Utilitrak® 3 wheels carriage, Polymer roller carriage



UTKpwr  
Utilitak® V rail, V rail



UTKpwcr  
Utilitrak® 3 wheels carriage, Polymer roller carriage