



# Magnetic stud with central hole

AlNiCo

VAP



- AlNiCo magnets with central through drilled mounting hole
- Both faces are machine finished and have a strong attraction force in a reduced size
- Working temperature -50°C to +450°C
- Good shock resistance

**For recessed mounting, following precautions should be observed**

- in a non-ferrous support: none specified
- in a ferrous support: magnet should be isolated from the support by an air gap or non-ferrous material

## Applications

- Suitable for fixing or positioning of components in reduced spaces and possibly subject to high temperatures
- Positioning of inserts in moulding machines...



## DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	Ød	E	F (daN)	Weight (g)	Stock*	Price each 1 to 5
VAP19-8	19	3,5	8,0	3,0	18	✓	6,65 €
VAP28-9	29	5,0	9,0	5,0	46	✓	10,62 €
VAP38-11	38	5,0	10,5	9,5	97	-	15,71 €

\*Depending on availability - Dimensions in mm


## Our other products



TBbutee  
Axial thrust bearing,  
Steel balls



LSAG  
Sleeve for splined ball  
shaft, Chariot - from  
514 N to 15386 N



RPPM  
RPP type belt per  
metre, RPP5 Steel  
cored polyurethane



CFF  
Female rod ends DIN  
ISO12240-4, Steel /  
bronze



SFWR  
End support, Surface  
mounting



OPFL\_OPPM  
Numerical counter  
accessories, Locking  
clamp



HTD5M-BAR  
HTD type tooth bar  
stock, HTD5



T10courroie  
T type timing belt,  
T10 Steel cored  
polyurethane



GGP  
Male wing knob,  
Technopolymer with  
brass spindle



ZHG5  
Plastic spur gear,  
Machined plastic  
(delrin)



SA\_SAKH  
Housing for linear  
bearing, Closed - light  
load



HSS  
Shoulder screw  
ISO7379, Hardened  
Steel class 12.9

## Complementary products



PLC\_PLT  
Magnetic stud with  
central hole, With  
central hole



PLC\_PLT  
Magnetic stud with  
threaded hole, With  
threaded hole