

Steel index bolt



SLB


Pull to unlock

- **Manual indexing bolt**
- Exists in 4 different versions
- **Materials:**
 - Bolt: Glass reinforced polyamide
 - Body: Blackened steel (class 5.8)
 - Tip: Hardened steel
 - Spring: Steel
- Working temp: -50°C to +130°C




Uses

- Locating and indexing
- Pull to retract locking pin.
- Turn through 90° to retain (Models C + D)



Normal

Retracted



MODEL A
Without lock nut
Without slot

MODEL B
With lock nut
Without slot

MODEL C
Without lock nut
With slot

MODEL D
With lock nut
With slot

DISCOUNTS

Qty	1+	6+	20+
Disc.	List -10%	On request	

Part number	D	D1	D2	L	L1	L2	L3	H	SW1	SW2	F x 30°	Spring strength		Price each 1 to 5	
												initial F1 (N)	final F2 (N)		
SLB10-A	5	M10x1,0	21	47	17	7	15	5	13	-	1,3	5	12	✓	11,36 €
SLB10-B	5	M10x1,0	21	47	17	7	15	5	13	17	1,3	5	12	✓	11,73 €
SLB10-C	5	M10x1,0	21	47	17	7	15	5	13	-	1,3	5	12	✓	14,37 €
SLB10-D	5	M10x1,0	21	47	17	7	15	5	13	17	1,3	5	12	✓	14,50 €
SLB12-A	6	M12x1,5	25	56	20	8	17	6	14	-	1,8	6	14	✓	12,67 €
SLB12-B	6	M12x1,5	25	56	20	8	17	6	14	19	1,8	6	14	✓	13,05 €
SLB12-C	6	M12x1,5	25	56	20	8	17	6	14	-	1,8	6	14	✓	15,92 €
SLB12-D	6	M12x1,5	25	56	20	8	17	6	14	19	1,8	6	14	✓	16,33 €
SLB16-A	8	M16x1,5	33	74	26	10	23	8	19	-	2,3	15	35	✓	16,33 €
SLB16-B	8	M16x1,5	33	74	26	10	23	8	19	24	2,3	15	35	✓	17,43 €
SLB16-C	8	M16x1,5	33	74	26	10	23	8	19	-	2,3	15	35	✓	19,07 €
SLB16-D	8	M16x1,5	33	74	26	10	23	8	19	24	2,3	15	35	✓	20,16 €
SLB20-A	10	M20x1,5	33	80	28	12	25	10	22	-	2,8	15	40	✓	23,62 €
SLB20-B	10	M20x1,5	33	80	28	12	25	10	22	30	2,8	15	40	✓	24,73 €
SLB20-C	10	M20x1,5	33	80	28	12	25	10	22	-	2,8	15	40	✓	30,92 €
SLB20-D	10	M20x1,5	33	80	28	12	25	10	22	30	2,8	15	40	✓	32,00 €

*Depending on availability - Dimensions in mm

Our other products



GLB
Small 6 lobe threaded handle - female, Technopolymer - Stainless steel



SLB
Indexing plunger, steel class 5.8



CHC
Socket headed screw, Steel class 12.19



PRF_PGN
Door handle for aluminium profile, Handle with lock suitable



BOX-NINA
Self locking nut - DIN985, Box set of steel nuts



PAMF80EB
Articulated foot with sheet metal base Ø80, Articulated foot



BH01
Single housed bearing, Bearing fitted with adhesive



T5P_T10P
Connecting plate for T type timing belts, T10



G-ECO
Eco range Spur gear, Steel C45



SVG
Adjustable latch clamp with strike plate, Stroke from



RFVcap
Stainless steel protective cover, Open protective cover



NSP
Right angled support clamp, Right angled support clamp

Complementary products



SLBE
Indexing plunger - Spacer, Spacer for SLB and SLBS index bolts