

# Steel index bolt



## SLB


## Pull to unlock

- **Manual indexing bolt**
- Exists in 4 different versions
- **Materials:**
  - Bolt: Glass reinforced polyamide
  - Body: Blackened steel (class 5.8)
  - Tip: Hardened steel
  - Spring: Steel
- Working temp: -50°C to +130°C




### Uses

- Locating and indexing
- Pull to retract locking pin.
- Turn through 90° to retain (Models C + D)



Normal Retracted



### DISCOUNTS

Qty	1+	6+	20+
Disc.	List -10%	On request	On request

Part number	D	D1	D2	L	L1	L2	L3	H	SW1	SW2	F x 30°	Spring strength		Price each 1 to 5	
												initial F1 (N)	final F2 (N)		
SLB10-A	5	M10x1,0	21	47	17	7	15	5	13	-	1,3	5	12	✓	11,36 €
SLB10-B	5	M10x1,0	21	47	17	7	15	5	13	17	1,3	5	12	✓	11,73 €
SLB10-C	5	M10x1,0	21	47	17	7	15	5	13	-	1,3	5	12	✓	14,37 €
SLB10-D	5	M10x1,0	21	47	17	7	15	5	13	17	1,3	5	12	✓	14,50 €
SLB12-A	6	M12x1,5	25	56	20	8	17	6	14	-	1,8	6	14	✓	12,67 €
SLB12-B	6	M12x1,5	25	56	20	8	17	6	14	19	1,8	6	14	✓	13,05 €
SLB12-C	6	M12x1,5	25	56	20	8	17	6	14	-	1,8	6	14	✓	15,92 €
SLB12-D	6	M12x1,5	25	56	20	8	17	6	14	19	1,8	6	14	✓	16,33 €
SLB16-A	8	M16x1,5	33	74	26	10	23	8	19	-	2,3	15	35	✓	16,33 €
SLB16-B	8	M16x1,5	33	74	26	10	23	8	19	24	2,3	15	35	✓	17,43 €
SLB16-C	8	M16x1,5	33	74	26	10	23	8	19	-	2,3	15	35	✓	19,07 €
SLB16-D	8	M16x1,5	33	74	26	10	23	8	19	24	2,3	15	35	✓	20,16 €
SLB20-A	10	M20x1,5	33	80	28	12	25	10	22	-	2,8	15	40	✓	23,62 €
SLB20-B	10	M20x1,5	33	80	28	12	25	10	22	30	2,8	15	40	✓	24,73 €
SLB20-C	10	M20x1,5	33	80	28	12	25	10	22	-	2,8	15	40	✓	30,92 €
SLB20-D	10	M20x1,5	33	80	28	12	25	10	22	30	2,8	15	40	✓	32,00 €

\*Depending on availability - Dimensions in mm

## Our other products



LVT

Miniature motorised actuator 1A, 1 ampere



H02

Single needle roller universal joint, Heavy duty



BOX-CSss

Hose clamp, Box set of stainless steel hose clamps



CLG2

Moulded plastic spur gear, Moulded plastic (nylon)



CHAFR

Adjustable friction hinges, Friction



VCMB

Dual-thread screw wood/metal, Stainless steel



RBN

Wheel, Rubber tyre - Polypropylene rim



T5M T10M

T type timing belt per metre, T5 Steel cored polyurethane



BPM

Slotted spring plunger with ball tip, Stainless



MLY

Bow shackle with eye bolt, Steel



SUPTOOL

Installation tools for clamping hub, For



DB

Steel bevel gear, 2:1

## Complementary products



SLBE

Indexing plunger - Spacer, Spacer for SLB and SLBS index bolts



SDC

Positioning sleeve for indexing pin, For pin Ø4 to Ø12



SDCss

Positioning sleeve for indexing pin, For pin Ø4 to Ø12