

Spacer for index bolt

SLBE

Used with SLB and SLBS




- Allows the length of the thread of index bolts to be adapted to the length required for an application (wall thickness)
- Material:
stainless steel, natural finish

Accessories

- Used with SLB and SLBS index bolts
SLB and SLBS

Info

- Not sold individually,
contact us for details



DISCOUNTS

Qty	1+	40+	100+	200+
Disc. List	-5%	-10%	On request	

Part number	ØD	ØD1	Length L (mm)	Weight (kg)	Price each 1 to 39
SLBE8-11-2/SS	8	11	2	0,6	0,59 €
SLBE8-11-3/SS	8	11	3	0,9	0,62 €
SLBE8-11-4/SS	8	11	4	1,3	0,68 €
SLBE8-11-6/SS	8	11	6	2,0	0,72 €
SLBE8-11-8/SS	8	11	8	2,6	0,78 €
SLBE10-14-2/SS	10	14	2	1,1	0,62 €
SLBE10-14-3/SS	10	14	3	1,7	0,72 €
SLBE10-14-4/SS	10	14	4	2,2	0,72 €
SLBE10-14-6/SS	10	14	6	3,4	0,78 €
SLBE10-14-8/SS	10	14	8	4,5	0,87 €
SLBE12-15-2/SS	12	15	2	0,9	0,68 €
SLBE12-15-4/SS	12	15	4	1,9	0,78 €
SLBE12-15-5/SS	12	15	5	2,4	0,84 €
SLBE12-15-6/SS	12	15	6	2,8	0,87 €
SLBE12-15-8/SS	12	15	8	3,8	0,97 €
SLBE12-17-2/SS	12	17	2	1,6	0,78 €
SLBE12-17-4/SS	12	17	4	3,4	0,87 €
SLBE12-17-5/SS	12	17	5	4,3	0,97 €
SLBE12-17-6/SS	12	17	6	5,2	1,00 €
SLBE12-17-8/SS	12	17	8	6,9	1,08 €
SLBE16-21-4/SS	16	21	4	4,4	1,00 €
SLBE16-21-5/SS	16	21	5	5,5	1,08 €
SLBE16-21-6/SS	16	21	6	6,6	1,17 €
SLBE16-21-8/SS	16	21	8	8,8	1,26 €
SLBE16-21-10/SS	16	21	10	11,0	1,32 €

Dimensions in mm

Our other products



ACM_TRI

Manual bonnet fastener, Black rubber fastener




ERC

Quick fitting cable terminal, Eye version



BDP1R

Adjustable support arm, Single clamp



EPRF

High helix leadscrew, Flanged nut - up to 40mm per rotation




CHB

Single output shaft, For CHB gearbox



STL

Guidance brush - Rail, Rail



SBF

Open flange bearing unit for food industry, cover



V3RA_PT

3-spoked handwheel with handle, Polyamide




BPVMss

Stainless steel miniature ball transfer



PPF

Indexing plunger with flange, with drilled



GBMf

Flanged leadscrew nut, Flanged nut -



NPTF20

Fixed tube carrier, Fixed Ø10 to Ø14

Complementary products



SLB

Indexing plunger, steel class 5.8



SLB

Indexing plunger, steel class 5.8



SLB

Indexing plunger, steel class 5.8



SLB

Indexing plunger, steel class 5.8