



- Locating bolt for manual indexing applications
- Exists in 4 versions
- Material:
 - Body: Stainless steel 303
 - Pin: Hardened stainless steel 420
- Finish:
 - Ground and blackened
 - Mushroom headed button: Electropolished finish




Info.


- These locating bolts can be used to restrict lateral movement. Raising the button releases the pin




Form A
Without slot,
without lock
nut



Form B
Without slot,
with lock nut



Form C
With slot,
without lock nut



Form D
With slot,
with lock nut

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	ØD	ØD1	ØD2	L	L1	L2	L3	H	SW1	SW2	Spring strength				Price each 1 to 5
											F x 30°	initial (N)	final (N)	Stock	
SLBS8-A	4	M8 x 1,0	18	43,0	15	6	13	4	10	13	1,0	6	12	✓	20,50 €
SLBS8-B	4	M8 x 1,0	18	43,0	15	6	13	4	10	13	1,0	6	12	✓	22,58 €
SLBS8-C	4	M8 x 1,0	18	38,5	15	6	13	4	10	13	1,0	6	12	✓	24,63 €
SLBS8-D	4	M8 x 1,0	18	38,5	15	6	13	4	10	13	1,0	6	12	✓	27,00 €
SLBS10-A	5	M10 x 1,0	21	50,0	17	7	15	5	13	17	1,3	5	12	✓	19,50 €
SLBS10-B	5	M10 x 1,0	21	50,0	17	7	15	5	13	17	1,3	5	12	✓	21,57 €
SLBS10-C	5	M10 x 1,0	21	43,5	17	7	15	5	13	17	1,3	5	12	-	23,49 €
SLBS10-D	5	M10 x 1,0	21	43,5	17	7	15	5	13	17	1,3	5	12	✓	25,70 €
SLBS12-A	6	M12 x 1,5	25	59,0	20	8	17	6	14	19	1,8	6	14	✓	23,03 €
SLBS12-B	6	M12 x 1,5	25	59,0	20	8	17	6	14	19	1,8	6	14	✓	25,30 €
SLBS12-C	6	M12 x 1,5	25	52,0	20	8	17	6	14	19	1,8	6	14	✓	27,77 €
SLBS12-D	6	M12 x 1,5	25	52,0	20	8	17	6	14	19	1,8	6	14	✓	30,32 €
SLBS16-A	8	M16 x 1,5	33	77,0	26	10	23	8	19	24	2,3	15	35	✓	30,55 €
SLBS16-B	8	M16 x 1,5	33	77,0	26	10	23	8	19	24	2,3	15	35	✓	33,79 €
SLBS16-C	8	M16 x 1,5	33	68,0	26	10	23	8	19	24	2,3	15	35	✓	37,73 €
SLBS16-D	8	M16 x 1,5	33	68,0	26	10	23	8	19	24	2,3	15	35	✓	41,32 €
SLBS20-A	10	M20 x 1,5	33	83,0	28	12	25	10	22	30	2,6	15	40	-	52,20 €
SLBS20-B	10	M20 x 1,5	33	83,0	28	12	25	10	22	30	2,6	15	40	✓	55,88 €
SLBS20-C	10	M20 x 1,5	33	74,0	28	12	25	10	22	30	2,6	15	40	-	72,70 €
SLBS20-D	10	M20 x 1,5	33	74,0	28	12	25	10	22	30	2,6	15	40	✓	76,57 €

*Depending on availability - Dimensions in mm

Our other products



PCS_PA6

Plastic sprocket,
12.7mm (DIN 08B-1)



BH01

Single housed
bearing, Bearing fitted
with adhesive



SVR30

Screwjack with
travelling nut, with
moving nut



P40

Worm and wheel gear
reducer, up to 18 Nm



LOQ

Manual lock, Manual
latch



PF40NM

Worm and wheel gear
reducer, up to 18 Nm



BABA

Ball pin lifting ring,
Steel



UTKpwc

Utilitrak® 3 wheels
carriage, Polymer
series V wheels



DH

Dowel pin, Solid DIN
6325



LVT

Miniature motorised
actuator 1A, 1 ampere



PRF_CLIP_45

Cable clip for
aluminium profile, For
cable chute



SEV

Vertical stirrup toggle
clamp, Vertical Latch
Clamp - steel

Complementary products



SLBE

Indexing plunger -
Spacer, Spacer for
SLB and SLBS index
bolts



SDC

Positioning sleeve for
indexing pin, For pin
Ø4 to Ø12



SDC_{ss}

Positioning sleeve for
indexing pin, For pin
Ø4 to Ø12



PITAss

Locking bolt, with T
handle