


Stainless steel 304L

Ratio
2:1
3:1
4:1

- Module 0.8 to 2.5
- Teeth Gleason
- Material:
stainless steel 304L
- Pressure angle 20°



stainless steel

TORQUE AND POWER INDICATION	For 20 teeth at 1000 rpm					
	2.5 MOD	2.0 MOD	1.5 MOD	1.25 MOD	1.0 MOD	0.8 MOD
Torque (Nm)	4.30	2.20	0.94	0.71	0.57	0.14
Power (kW)	0.455	0.231	0.097	0.08	0.03	0.015

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	Teeth		Z	Module	ØP	E	ØD	ØA	ØM	F	G	H	Screw		Price each 1 to 5
	Z	Module											R	T	
SSDB0.8-15	15	0,8	12,00	20,00	13,93	6	10	11,90	7,50	4,02	M3	3,50	46,73	€	
SSDB0.8-30	30		24,00	14,00	24,64	8	20	10,08	5,50	4,02	M3	3,50	55,09	€	
SSDB1-15	15	2:1	15,00	24,00	17,42	8	14	13,87	8,76	5,03	M4	4,00	52,99	€	
SSDB1-30	30	1	30,00	18,00	30,58	10	25	13,11	7,00	5,03	M4	4,00	65,15	€	
SSDB1.5-15	15	1,5	22,50	35,00	26,12	10	21	19,84	12,13	7,55	M4	5,00	57,68	€	
SSDB1.5-30	30		45,00	27,00	45,87	10	30	19,66	11,00	7,55	M4	5,00	74,05	€	
SSDB2-15	15	2	30,00	45,00	34,83	12	28	24,76	14,86	10,06	M5	7,50	63,95	€	
SSDB2-30	30		60,00	35,00	61,16	12	40	25,21	14,00	10,06	M5	8,00	88,65	€	
SSDB2.5-15	15	2,5	37,50	54,00	43,54	15	32	29,51	16,51	13,53	M5	8,00	87,37	€	
SSDB2.5-30	30		75,00	41,50	76,45	15	30	29,31	13,31	13,53	M5	7,00	121,37	€	
SSTB0.8-15	15	0,8	12,00	28,00	14,14	6	10	15,63	9,67	5,69	M3	5,00			
SSTB0.8-45	45		36,00	20,00	36,30	8	28	16,07	8,00	5,69	M3	4,00			
SSTB1-15	15	3:1	15,00	32,00	17,67	8	13	16,54	9,18	7,12	M4	4,50			
SSTB1-45	45	1	45,00	24,00	45,37	10	40	19,09	10,00	7,12	M4	5,00			
SSTB1.5-15	15	1,5	22,50	45,00	26,51	10	18	21,80	10,51	10,67	M4	5,00			
SSTB1.5-45	45		67,50	32,00	68,06	15	50	24,63	12,00	10,67	M4	6,00			
SSFB0.8-15	15	0,8	12,00	35,00	14,23	6	10	18,07	10,58	7,10	M3	5,00			
SSFB0.8-60	60		48,00	20,00	48,22	8	30	15,98	8,00	7,10	M3	4,00			
SSFB1-15	15	4:1	15,00	45,00	17,79	8	13	24,22	14,73	9,28	M4	7,00			
SSFB1-60	60	1	60,00	30,00	60,27	10	40	25,08	12,00	9,28	M4	6,00			
SSFB1.5-15	15	1,5	22,50	60,00	26,69	10	18	28,82	12,08	13,91	M4	6,00			
SSFB1.5-60	60		60,00	35,00	90,41	15	50	27,61	12,00	13,91	M4	6,00			

Dimensions in mm

On request

Our other products



M0

Worm, Hardened steel



SER

Magnetic doorstop for aluminium profile, Magnetic doorstop



CHML63

Worm and wheel gear reducer, up to 138 Nm - Integrated torque limiter



CHAL3

Piano hinge, Steel



BWU

Compact precision slide, from 1510 N to 10500 N



PW_PWG25

Worm - precision range, Stainless steel



BIM

Indexing plunger mini, miniature



EKONSL

Silicone conical elasto buffer, Female mounting



EHD16

Internal epicyclic servo reducers, from 210 to 380 Nm



TMR

Rigid manual tensioner, Adjustable



DBC

Panamech, Multi-Beam, Aluminium - with clamping jaw



PAT123

Pressed stainless steel articulating foot Ø123, Ø 123

Complementary products



DB

Steel bevel gear, 2:1



ZDB

Machined plastic bevel gear, 2:1