

Small 6 lobe threaded handle



VP

Black Duroplast, steel thread

- **Operating element**

- **Materials:**

Black phenolic Duraplast


Threaded stud: chromed steel

Good resistance



Advantages

- Easy grip
- Temperature resistant
- Good chemical resistance
- Easier to clean that technopolymer
- In machining applications, less likely to retain swarf



DISCOUNTS

Qty	1+	10+	20+	50+	100+	200+
Disc. List		-5%	-10%	-15%	-20%	On request

Part number	ØA	ØB	C	ØD	F	G	L	Weight (g)	Price each 1 to 9
VP20-M4-15	20	13	15	M4	7	8	15	5	2,73 €
VP20-M4-25	20	13	15	M4	7	8	25	6	2,73 €
VP20-M5-15	20	13	15	M5	7	8	15	7	2,95 €
VP20-M5-25	20	13	15	M5	7	8	25	8	3,02 €
VP20-M6-15	20	13	15	M6	7	8	15	8	2,95 €
VP20-M6-25	20	13	15	M6	7	8	25	11	3,02 €
VP30-M6-15	30	17	24	M6	11	13	15	18	3,46 €
VP30-M6-25	30	17	24	M6	11	13	25	21	3,54 €
VP30-M6-35	30	17	24	M6	11	13	35	23	3,61 €
VP30-M8-20	30	17	24	M8	11	13	20	25	3,73 €
VP30-M8-30	30	17	24	M8	11	13	30	27	3,73 €
VP40-M8-20	40	21	28	M8	13	15	20	38	4,61 €
VP40-M8-30	40	21	28	M8	13	15	30	40	4,68 €
VP40-M8-40	40	21	28	M8	13	15	40	44	4,75 €
VP50-M8-20	50	25	33	M8	15	18	20	52	5,37 €
VP50-M8-30	50	25	33	M8	15	18	30	56	5,41 €
VP50-M8-40	50	25	33	M8	15	18	40	60	5,41 €
VP50-M10-20	50	25	33	M10	15	18	20	61	5,48 €
VP50-M10-30	50	25	33	M10	15	18	30	65	5,63 €
VP50-M10-40	50	25	33	M10	15	18	40	70	6,00 €
VP60-M12-20	60	28	35	M12	15	20	20	101	7,56 €
VP60-M12-30	60	28	35	M12	15	20	30	107	7,71 €
VP60-M12-40	60	28	35	M12	15	20	40	115	7,75 €
VP70-M12-30	70	32	42	M12	21	21	30	133	9,29 €
VP70-M12-40	70	32	42	M12	21	21	40	138	9,44 €
VP70-M12-50	70	32	42	M12	21	21	50	145	9,58 €
VP70-M14-50	70	32	42	M14	21	21	50	181	13,20 €

Dimensions in mm

Our other products



M0
Worm and wheel set,
Hardened steel



PV1R
Adjustable suction-
cup support, Standard
grip



PSG08HC
Skive hobbled spur
gears - precision
range, Case hardened
steel 20NCD2



BR65C
Half-articulated foot Ø
65, Ø 65



TCLar
Automatic chain
tensioner, With wide
guide



SUPss
Self-centering
clamping hub
stainless steel,
Without locknut



UCFL_PBT
Stainless
steel/Polymer flanged
bearing, Polymer and
stainless steel



BPHR
Ball transfer unit
housed spring loaded,
High



MFBS
Stainless steel flexible
bellows coupling,



M0
Worm and wheel set,
Machined plastic



MCLred
Reducing sleeve
female/female,



PCP
Cell carrier assembly,
Ready assembled

Complementary products



GLP
Small 6 lobe threaded
handle - male,
Technopolymer - Steel



VPSS
Small 6 lobe threaded
handle - male,
Duroplast - Stainless
steel