


# Magnetic head screw

## VTAP

## With rubber coating

- **Magnetic screw with rubber coating**
- With magnet incorporated in the screw head
- According to DIN EN ISO 4017-8,8
- Temperature of use: Max. 80°C
- Materials:
  - Zinc-plated steel body
  - NdFeB Magnet



### DISCOUNTS

Qty	1+	5+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØM	ØD	L	H	SW	F (N)	Weight (g)	Price each 1 to 4
VTAP6-13	M6	13	10	16	11	15	13	17,14 €
VTAP8-16	M8	16	12	18	13	23	23	20,55 €
VTAP10-20	M10	20	14	20	17	46	44	25,29 €

\*Depending on availability - Tolerances +/-0.2mm - Dimensions in mm

# Magnetic screw with socket


Steel

HCA


- **Magnetic screw with socket hexagonal head**
- With magnet incorporated at the end of the screw.
- According to DIN EN ISO 4017-8,8
- Temperature of use: Max. 80°C
- Materials:  
Zinc-plated steel body  
NdFeB Magnet

## Application

- Sensor counter
- Fixtures



Example of use:  
Fixtures



## DISCOUNTS

Qty	1+	5+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØM	L	S	F (N)	Weight (g)	Price each 1 to 4
HCA6-12	M6	12	3	2,5	2	6,73 €
HCA6-16	M6	16	3	2,5	3	6,80 €
HCA6-20	M6	20	3	2,5	4	6,87 €
HCA6-25	M6	25	3	2,5	5	7,01 €
HCA6-30	M6	30	3	2,5	6	7,08 €
HCA8-16	M8	16	4	7,0	6	7,01 €
HCA8-20	M8	20	4	7,0	8	7,15 €
HCA8-25	M8	25	4	7,0	10	7,23 €
HCA8-30	M8	30	4	7,0	11	7,38 €
HCA8-40	M8	40	4	7,0	15	7,74 €
HCA10-20	M10	20	5	11,0	12	7,52 €
HCA10-25	M10	25	5	11,0	15	7,74 €
HCA10-30	M10	30	5	11,0	18	7,85 €
HCA10-40	M10	40	5	11,0	24	8,20 €
HCA10-50	M10	50	5	11,0	30	8,64 €
HCA12-25	M12	25	6	17,0	21	8,35 €
HCA12-30	M12	30	6	17,0	25	8,57 €
HCA12-40	M12	40	6	17,0	34	9,07 €
HCA12-50	M12	50	6	17,0	43	9,54 €
HCA12-60	M12	60	6	17,0	52	10,04 €
HCA16-30	M16	30	8	35,0	45	11,02 €
HCA16-40	M16	40	8	35,0	60	11,66 €
HCA16-50	M16	50	8	35,0	76	12,35 €
HCA16-60	M16	60	8	35,0	92	13,00 €
HCA16-80	M16	80	8	35,0	123	14,33 €

\*Depending on availability - Dimensions in mm

# Magnetic screw with hexagonal head

## VTHA


## Steel

- **Magnetic screw with hexagonal head**
- With magnet incorporated in the screw head
- According to DIN EN ISO 4017-8,8
- Temperature of use: Max. 80°C
- Materials:
  - Zinc-plated steel body
  - NdFeB Magnet




### Application

- Sensor counter
- Fixtures



Example of use:  
Fixtures



### DISCOUNTS

Qty	1+	5+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØM	L	K	A/F	F (N)	Weight (g)	Price each
VTHA6-12	M6	12	4,3	10	25	6	7,59 €
VTHA6-16	M6	16	4,3	10	25	6	7,66 €
VTHA6-20	M6	20	4,3	10	25	7	7,74 €
VTHA6-25	M6	25	4,3	10	25	8	7,85 €
VTHA6-30	M6	30	4,3	10	25	10	7,92 €

\*Depending on availability - Dimensions in mm

## DISCOUNTS

Qty	1+	5+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØM	L	K	A/F	F (N)	Weight (g)	Price each 1 to 4
VTHA8-16	M8	16	4,3	13	50	11	8,28 €
VTHA8-20	M8	20	4,3	13	50	12	8,43 €
VTHA8-25	M8	25	4,3	13	50	15	8,50 €
VTHA8-30	M8	30	4,3	13	50	17	8,64 €
VTHA8-40	M8	40	4,3	13	50	21	9,00 €
VTHA10-20	M10	20	6,3	17	75	24	9,75 €
VTHA10-25	M10	25	6,3	17	75	27	9,90 €
VTHA10-30	M10	30	6,3	17	75	31	10,04 €
VTHA10-40	M10	40	6,3	17	75	37	10,47 €
VTHA10-50	M10	50	6,3	17	75	43	10,81 €
VTHA12-25	M12	25	7,5	19	110	40	11,38 €
VTHA12-30	M12	30	7,5	19	110	45	11,59 €
VTHA12-40	M12	40	7,5	19	110	54	11,73 €
VTHA12-50	M12	50	7,5	19	110	62	12,20 €
VTHA12-60	M12	60	7,5	19	110	71	12,70 €
VTHA16-30	M16	30	10,0	24	145	86	13,90 €
VTHA16-40	M16	40	10,0	24	145	100	14,62 €
VTHA16-50	M16	50	10,0	24	145	117	14,62 €
VTHA16-60	M16	60	10,0	24	145	133	15,95 €
VTHA16-80	M16	80	10,0	24	145	165	17,28 €

\*Depending on availability - Dimensions in mm

## Our other products



ACLBTS

Spherical ended stop for aluminium profile, Spherical ended stop



ACLBTS

Closing system for aluminium profile, 90° bracket for spherical end...



CNA-CNG

Right angled mounting plate, Right angled mounting plate for clevis



CHA\_GC\_14SS

Stainless steel garnet hinge, To screw



BGC

Oldham coupling, Clamp



UGH25

H Type Guide units, For Ø25 actuators



M0

Worm and wheel set, Bronze



AT5M AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane




HK

Manual locking clamp, Manual locking clamp LRX



CHTRP

Single and dual output gearboxes, Up to 28,8 Nm



ACL-PR

Joining plate for aluminium profile, Right angled



RAG-12-M8

Roller guide accessory, Anchoring system

## Complementary products



VTAP

Magnetic head screw, With rubber coating With rubber coating



HCA

Magnetic screw with socket, Steel